



# SCHUNK chuck jaws for ROTA THW3 500–165


## Base Jaws

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | b<br>[mm] | Screws | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|--------|---------------|
|  | GBK 500     | 0159104 | 30        | 18        | 45        | 57        | 160       | 60        | M16    | 8.6           |


## Claw jaws for I.D. clamping

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|----|-----------|--------|----------|---------------|
|  | SZKI 411    | 0166168 | 18        | 30        | 50        | 71        | 33        | M8 | 60        | M16    | Steel    | 5.5           |
|                                                                                   | SZKI 409    | 0166166 | 18        | 30        | 60        | 71        | 33        | M8 | 60        | M16    | Steel    | 6             |
|                                                                                   | SZKI 411    | 0166168 | 18        | 30        | 50        | 71        | 33        | M8 | 60        | M16    | Steel    | 5.5           |


## Claw jaws for O.D. clamping

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|----|-----------|--------|----------|---------------|
|  | SZKA 412    | 0139173 | 18        | 30        | 50        | 71        | 33        | M8 | 60        | M16    | Steel    | 5.1           |
|                                                                                   | SZKA 409    | 0139170 | 18        | 30        | 50        | 71        | 33        | M8 | 60        | M16    | Steel    | 6             |
|                                                                                   | SZKA 412    | 0139173 | 18        | 30        | 50        | 71        | 33        | M8 | 60        | M16    | Steel    | 5.1           |


## Hard Stepped Block Jaws

|                                                                                     | Description | ID      | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|-----------|----------|---------------|
|  | GST 500-630 | 0162104 | 45        | 93        | 46         | 175       | 20        | Steel    | 11.7          |

## Hard Stepped Top Jaws

|                                                                                     | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHF 400     | 0155104 | 18        | 30        | 45        | 82        | 75         | 130       | 20        | 60        | M16    | Steel    | 6.8           |

## Pendulum jaws


|                                                                                     | Description  | ID      | H<br>[mm] | T<br>[mm] | m/piece<br>[kg] |
|-------------------------------------------------------------------------------------|--------------|---------|-----------|-----------|-----------------|
|  | PNK-G 500-2  | 0190625 | 118       | 50        | 4.4             |
|                                                                                     | PNK-G 500-4  | 0190627 | 118       | 50        | 5.5             |
|                                                                                     | PNK-G 500-6  | 0190629 | 118       | 50        | 5.8             |
|                                                                                     | PNK-G 500-8  | 0190631 | 118       | 50        | 6.2             |
|                                                                                     | PNK-G 500-10 | 0190633 | 118       | 50        | 8.3             |




Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for ROTA THW3 500–165



## Soft Full Grip Jaws

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|------------|-------------|-----------|------------|------------|-----------|------------|-----------|--------|----------|---------------|
|  | SFA-SM 400  | 0173104 | 18        | 30        | 330       | 150        | 440         | 85        | 78         | 55         | 160       | 95         | 60        | M16    | Steel    | 55.6          |
|                                                                                   | SFA-SA 400  | 0174104 | 18        | 30        | 330       | 150        | 440         | 90        | 83         | 60         | 160       | 95         | 60        | M16    | Aluminum | 22.8          |

## Soft Monoblock Jaws

|                                                                                   | Description | ID      | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|----------|---------------|
|  | UVB 500     | 0164104 | 45        | 124       | 77         | 175       | Steel    | 20.3          |

## Soft Top Jaws

|                                                                                     | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|------------|-----------|------------|-----------|--------|----------|---------------|
|  | SFA 400     | 0153104 | 18        | 30        | 50        | 80        | 73         |            | 180       | 50         | 60        | M16    | Steel    | 13.5          |
|                                                                                     | SFA 400-C1  | 0154116 | 18        | 30        | 60        |           | 80         | 73         | 130       | 35         | 60        | M16    | Steel    | 11.8          |
|                                                                                     | SFA 400-C3  | 0154118 | 18        | 30        | 60        |           | 100        | 93         | 155       | 35         | 60        | M16    | Steel    | 21.5          |
|                                                                                     | SFA 400-C4  | 0154119 | 18        | 30        | 60        |           | 120        | 113        | 155       | 35         | 60        | M16    | Steel    | 22.4          |
|                                                                                     | SFA 400-C5  | 0154120 | 18        | 30        | 80        |           | 80         | 73         | 130       | 35         | 60        | M16    | Steel    | 16            |
|                                                                                     | SFA 400-C6  | 0154125 | 18        | 30        | 58        |           | 180        | 173        | 160       | 35         | 60        | M16    | Steel    | 35.1          |
|                                                                                     | SFA 400-C7  | 0154135 | 18        | 30        | 96        |           | 115        | 108        | 115       | 35         | 60        | M16    | Steel    | 25.9          |
|  | SFA-AL 400  | 0172105 | 18        | 30        | 50        | 80        | 73         |            | 180       | 50         | 60        | M16    | Aluminum | 5.1           |



Technical advice and sales: Tel. +49-7133-103-2750