




Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	SFGX 165	0149300	18	8	20	29.5	64	32	M8	0.7


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	22 – 54	201	SZKA-ST 161	0182150	8	18	22	40	30	32	M8	Steel	0.8


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	50 – 79	202	I	SZKI 167	0166150	8	18	35	40	20	M6	32	M8	Steel	0.9
	55 – 83	202	I	SZKI 168	0166151	8	18	35	40	20	M6	32	M8	Steel	1.4
	98 – 139	201	I	SZKI 169	0166152	8	18	30	40	20	M6	32	M8	Steel	1.3
	50 – 63	200	II	SZKI 167	0166150	8	18	35	40	20	M6	32	M8	Steel	0.9
	55 – 68	200	II	SZKI 168	0166151	8	18	35	40	20	M6	32	M8	Steel	1.4
	83 – 123	200	II	SZKI 169	0166152	8	18	30	40	20	M6	32	M8	Steel	1.3

Claw jaws for O.D. clamping



	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	87 – 128	212	I	SZKA 163	0165146	8	18	40	40	20	M6	32	M8	Steel	1
	138 – 179	242	I	SZKA 167	0165150	8	18	30	40	20	M6	32	M8	Steel	1.3
	143 – 184	242	I	SZKA 168	0165151	8	18	30	40	20	M6	32	M8	Steel	1.3
	39 – 80	202	I	SZKA 169	0165174	8	18	26	40	20	M6	32	M8	Steel	1
	71 – 112	201	II	SZKA 163	0165146	8	18	40	40	20	M6	32	M8	Steel	1
	122 – 163	226	II	SZKA 167	0165150	8	18	30	40	20	M6	32	M8	Steel	1.3
	127 – 168	226		SZKA 168	0165151	8	18	30	40	20	M6	32	M8	Steel	1.3
	32 – 64	201	II	SZKA 169	0165174	8	18	26	40	20	M6	32	M8	Steel	1

Hard Stepped Top Jaws



	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 160	0155100	8	18	20	36.5	32.5	63	7.5	32	M8	Steel	0.6
	SHF 160	0155100	8	18	20	36.5	32.5	63	7.5	32	M8	Steel	0.6



Soft Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 160	0173100	8	18	120	40	160	50	46	40	60	23	32	M8	Steel	4.8
	SFA-SA 160	0174100	8	18	120	40	165	50	46	40	59.5	23	32	M8	Aluminum	1.8

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 160	0153100	8	18	20	40	36		85	25	32	M8	Steel	1.2
	SFA 160-C1	0154121	8	18	30		55.5	51.5	85	19	32	M8	Steel	2.7
	SFA 160-C2	0154127	8	18	35		40	36	63	19	32	M8	Steel	1.6
	SFA 160-C3	0154131	8	18	40		60	56	70	19	32	M8	Steel	3.3
	SFA-AL 160	0172100	8	18	25	50	46		85	25	32	M8	Aluminum	0.7

