



Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	28 - 59	229	SZAJ-ST 20-2	0175503	14	35	45	38	25	M12	Steel	1.8



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	62 - 96	234	SZIJ 20-1	0179110	14	35	53	20	M6	25	M12	Steel	2
	92 - 126	236	SZIJ 20-2	0179111	14	40	53	20	M6	25	M12	Steel	2.1
	122 - 157	232	SZIJ 20-3	0179113	14	40	53	20	M6	25	M12	Steel	2.1
	152 - 187	242	SZIJ 20-4	0179114	14	40	53	20	M6	25	M12	Steel	2


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	46 - 81	230	SZAJ 20-1	0138110	14	35	53	25	M6	25	M12	Steel	1.9
	74 - 109	231	SZAJ 20-2	0138112	14	35	53	25	M6	25	M12	Steel	1.6
	104 - 139	231	SZAJ 20-3	0138114	14	40	53	25	M6	25	M12	Steel	1.7
	134 - 169	233	SZAJ 20-4	0138116	14	40	53	25	M6	25	M12	Steel	1.6
	156 - 191	250	SZAJ 20-16	0138143	14	40	53	25	M6	25	M12	Steel	1.7

Hard Stepped Top Jaws





	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	HSKN 215	0129101	14	36	52.5	81	12	25	21	21	M10	Steel	1.85
	SHB-J 80	0133109	14	35	51	87	12	15.5	25	25	M12	Steel	1.85
	SHB-J 82	0133110	14	32	38	79	12	16	25	25	M12	Steel	1.2

Pendulum jaws



	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	72 - 88	220	PNS-M 200-14-1	0160232	55	30	1.3
	102 - 132	249	PNS-M 200-14-2	0160233	55	30	1.5
	132 - 150	249	PNS-M 200-14-3	0160234	55	30	1.6



Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	M [mm]	a1 [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SKN 215	0127103	14	35	60	89	34		18	26		M10	Steel	3.6
	KM-WBL 80	0132601	14	35	40	102		4	20	25		M12	Steel	2.7
	KM-WBL 81	0132607	14	40	80	102		4	20	25		M12	Steel	6
	KM-WBL 82	0132615	14	40	100	102		4	20	25		M12	Steel	7.6
	SKNL 215	0128101	14	40	42	102	34	3	16	22	22	M10	Steel	2.9
	KM-WB 84	0132126	14	35	60	95			24	25		M12	Steel	3.9
	KM-WB 85	0132127	14	40	80	95			24	25		M12	Steel	6.1
	KM-WB 88	0132139	14	35	40	95			24	25		M12	Steel	2.7
	KM-WBAL 80	0132522	14	40	60	90			20	25		M12	Aluminum	1.5

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 82	0146131	14	20.5	8.5	25	M12	M12 x 30	70
	NJ 82 gesägt/ sawn	0146005	14	20.5	8.5		M12	M12 x 30	70

