



SCHUNK chuck jaws for KHL 160



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	HB 232	0121152	10	25	38	66	6.5	17	19	17	M10	Steel	0.7



Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 100	0112150	10	35	60	420	Steel	6.7

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-FB 232	0120200	10	30	45	70	4	13	19	M10	Steel	1.7
	FB-AL 140	0120550	10	25	50	70		13	19	M10	Aluminum	0.58

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	D [mm]	Max. adm. tightening torque [Nm]
	TS 10	0148106	10	20.3	9.3	M10		60
	TM 10	0148116		16		M10	16	60



Technical advice and sales: Tel. +49-7133-103-2750