


SCHUNK Spannbacken für 3QLK 250-72


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (Erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 41	0112112	21	50	60	90	15	28	M16	Stahl	2.1
	SBM 42	0112113	21	50	60	105	15	28	M16	Stahl	2.4
	SBM 4210	0112115	21	50	100	120	15	28	M16	Stahl	5
	SBM 4212	0112116	21	50	120	120	15	28	M16	Stahl	5.6
	SBM 4215	0112117	21	50	150	120	15	28	M16	Stahl	7
	SBM 428	0112114	21	50	80	120	15	28	M16	Stahl	3.7
	SBM 4281	0112137	21	50	80	150	15	28	M16	Stahl	4.6
	SBM 43	0112118	21	60	60	90	15	28	M16	Stahl	2.4
	SBM 44	0112119	21	60	60	105	15	28	M16	Stahl	2.9
	SBM 45	0112120	21	60	80	90	15	28	M16	Stahl	3.2
	SBM 46	0112121	21	60	80	105	15	28	M16	Stahl	3.8
	SBM 47	0112122	21	60	80	120	15	28	M16	Stahl	4.4
	SBM 48	0112123	21	80	60	90	15	28	M16	Stahl	3.2
	SBM 498	0112125	21	80	80	120	15	28	M16	Stahl	5.8


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 250	0121105	21	50	58	103.5	14	34	25	25	M16	Stahl	3.5

Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	55 - 103	275	SZA 25-37	0138180	21	50	58	25	M8	28	M16	Stahl	3.3
	94 - 143	276	SZA 25-38	0138181	21	50	58	25	M8	28	M16	Stahl	2.9
	144 - 192	279	SZA 25-39	0138182	21	50	58	25	M8	28	M16	Stahl	2.7
	190 - 240	314	SZA 25-40	0138183	21	50	58	25	M8	28	M16	Stahl	3.2
	46 - 80	285	SZA 31-10	0138184	21	50	58	25	M8	28	M16	Stahl	3.4
	90 - 138	287	SZA 31-11	0138185	21	50	58	25	M8	28	M16	Stahl	3.4
	155 - 204	285	SZA 31-12	0138186	21	50	58	25	M8	28	M16	Stahl	3.2
	218 - 267	345	SZA 31-13	0138187	21	50	58	25	M8	28	M16	Stahl	4.5

Krallenbacken für Innenspannung


	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	84 - 131	282	SZI 25-34	0123183	21	50	58	25	M8	28	M16	Stahl	3.5
	125 - 173	285	SZI 25-35	0123184	21	50	58	25	M8	28	M16	Stahl	3.2
	170 - 218	284	SZI 25-36	0123185	21	50	58	25	M8	28	M16	Stahl	3
	80 - 102	292	SZI 31-11	0123186	21	50	58	25	M8	28	M16	Stahl	4.1
	127 - 155	284	SZI 31-12	0123187	21	50	58	25	M8	28	M16	Stahl	4.2
	180 - 229	284	SZI 31-13	0123188	21	50	58	25	M8	28	M16	Stahl	3.9

SCHUNK Spannbacken für 3QLK 250-72



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	25 - 72	277	SZA-ST 25-2	0175103	21	45	50	40	28	M16	Stahl	2.7
	20 - 42	285	SZA-ST 31-1	0175104	21	45	50	40	28	M16	Stahl	3.3


Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	52 - 69	232	PNS-Z 250-21-1	0190105	64	35	1.9
	79 - 113	274	PNS-Z 250-21-2	0190106	64	35	2
	83 - 111	274	PNS-Z 250-21-3	0190107	64	35	2.1
	114 - 131	249	PNS-Z 250-21-4	0190108	64	35	2.3
	123 - 140	249	PNS-Z 250-21-5	0190109	64	35	2.3
	63 - 97	274	PNS-Z 315-1	0190110	64	35	2
	119 - 136	249	PNS-Z 315-3	0190112	64	35	2.5
	163 - 178	294	PNS-Z 315-4	0190113	64	35	2.7

Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-SM 250-21	0169103	21	180	104	250	70	55	80	30	28	M16	Stahl	14
	SWB-SM 251	0169107	21	180	104	250	100	85	80	30	28	M16	Stahl	21.7
	SWB-SA 250-21	0170103	21	180	70	250	78	63	87.5	40	28	M16	Aluminium	7.3
	SWB-SA 251	0170107	21	180	70	250	100	85	87.5	40	28	M16	Aluminium	8.3

Verzahnte Stangen





	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 210	0112180	21	50	60	420	Stahl	9.4
	SBM-ST 211	0112181	21	50	80	420	Stahl	12.7
	SBM-ST 212	0112182	21	50	120	420	Stahl	19.3
	SBM-ST 213	0112183	21	80	80	420	Stahl	20.4
	SBM-STA 210	0112184	21	50	80	420	Aluminium	4.6



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für 3QLK 250-72

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWBL 250-21	0120155	21	50	50	120	4	20	28	M16	Stahl	5.6
	CWB 251	0100012	21	50	60	95		15	28	M16	Stahl	5.2
	SWB 250	0120105	21	50	80	120		30	28	M16	Stahl	9.4
	SWB-AL 250	0168102	21	50	80	120		30	28	M16	Aluminium	3



Technische Beratung und Verkauf: Tel. +49-7133-103-2750