




Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	98 - 198	537	SZA-ST 40-1	0175105	25.5	60	55	45	35	M20	Steel	8



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	182 - 283	517	SZI 40-11	0123195	25.5	60	78	33	M8	35	M20	Steel	9
	180 - 280	553	SZI 40-12	0123196	25.5	60	78	33	M8	35	M20	Steel	10.2
	262 - 362	546	SZI 40-13	0123197	25.5	60	78	33	M8	35	M20	Steel	8.8
	341 - 442	546	SZI 40-14	0123198	25.5	60	78	33	M8	35	M20	Steel	7.5
	405 - 506	554	SZI 40-15	0123199	25.5	60	78	33	M8	35	M20	Steel	8.2

Claw jaws for O.D. clamping


	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	145 - 255	523	SZA 40-11	0138300	25.5	60	78	33	M8	35	M20	Steel	8
	131 - 231	576	SZA 40-12	0138301	25.5	60	78	33	M8	35	M20	Steel	11.5
	230 - 331	557	SZA 40-13	0138302	25.5	60	78	33	M8	35	M20	Steel	8
	314 - 415	537	SZA 40-14	0138303	25.5	60	78	33	M8	35	M20	Steel	8
	385 - 470	564	SZA 40-15	0138304	25.5	60	78	33	M8	35	M20	Steel	9.3
	465 - 566	667	SZA 40-16	0138305	25.5	60	78	33	M8	35	M20	Steel	11

Hard Stepped Top Jaws



	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 400	0121107	25.5	60	75	140	18	53	31	31	M20	Steel	8
	SP-HB 400-500	0125105	25.5	57	73	160	22	43.1	42	42	M18	Steel	10.2





Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a [mm]	Min. distance b [mm]	Screws	Material	m/piece [kg]
	SBM 50	0112126	25.5	60	60	140	20	35	M20	Steel	4
	SBM 51	0112127	25.5	60	80	140	20	35	M20	Steel	5
	SBM 52	0112128	25.5	60	100	140	20	35	M20	Steel	6.5
	SBM 53	0112129	25.5	60	100	155	20	35	M20	Steel	7.2
	SBM 531	0112138	25.5	60	100	195	20	35	M20	Steel	9.1
	SBM 5312	0112130	25.5	60	120	155	20	35	M20	Steel	8.7
	SBM 5315	0112131	25.5	58	160	155	20	35	M20	Steel	11.5
	SBM 5320	0112132	25.5	58	200	155	20	35	M20	Steel	14.2
	SBM 57	0112134	25.5	80	80	155	20	35	M20	Steel	7.2
	SBM 58	0112135	25.5	100	100	155	20	35	M20	Steel	11.6

Serrated bars



	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 250	0112190	25.5	60	100	420	Steel	19.2
	SBM-ST 251	0112191	25.5	58	160	420	Steel	30.9
	SBM-STA 250	0112187	25.5	60	100	420	Aluminum	7

Soft Full Grip Jaws


	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-SM 400	0169105	25.5	330	150	440	85	55	155	85	35	M20	Steel	55.2
	SWB-SA 400	0170105	25.5	330	150	440	98	68	160	85	35	M20	Aluminum	26.2



Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	CWB 400	0100008	25.5	60	80	140	30	35	M20	Steel	12.6
	SP-WB 400	0124105	25.5	60	100	155	35	40	M18	Steel	18.8
	SP-WB 500	0124106	25.5	60	100	195	37	40	M18	Steel	24.8
	SWB 400	0120107	25.5	60	90	155	30	35	M20	Steel	16
	SWB-AL 400	0168103	25.5	60	100	155	30	35	M20	Aluminum	6.4

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 181	0143105	25.5	34.5	14.5	M18	M18 x 55	220
	NS 205	0140123	25.5	34.5	14.5	M20	M20 x 45	240

