



SCHUNK chuck jaws for 3QLK 110-26

Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a [mm]	Min. distance b [mm]	Screws	Material	m/piece [kg]
	SBMJ 50	0132149	10	22	47	55	8	14	M8	Steel	0.4

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WB 45	0132102	10	25	32	55	4	13	14	M8	Steel	0.8
	KM-WB 46	0132103	10	22	47	55	4	13	14	M8	Steel	1
	KM-WB 54	0132111	10	25	32	57	4	10	18	M8	Steel	0.8
	KM-WB 55	0132136	10	22	47	55	4	10	18	M8	Steel	1
	KM-WB 56	0132137	10	22	47	55	4	10	19	M8	Steel	1



Technical advice and sales: Tel. +49-7133-103-2750