



Full grip jaws / Pie jaws

Height up to [mm]	Length up to [mm]	Wight up to [mm]	Price 3 p. set with order volume of:				Price 2 p. set with order volume of:		
			from 5 Sets 15 Pieces	from 3 Sets 9 Pieces	from 2 Sets 6 Pieces	from 1 Set 3 Pieces	from 5 Sets 10 Pieces	from 2 Sets 4 Pieces	from 1 Set 2 Pieces
			-40%	-30%	-20%	0%	-25%	-15%	0%
60	80	200	373 €	435 €	498 €	622 €	401 €	455 €	535 €
	150	300	468 €	546 €	624 €	780 €	480 €	544 €	640 €
	190	380	579 €	676 €	772 €	965 €	573 €	649 €	764 €
80	80	200	392 €	458 €	523 €	654 €	417 €	473 €	556 €
	150	300	526 €	614 €	702 €	877 €	529 €	599 €	705 €
	190	380	671 €	783 €	895 €	1.119 €	650 €	737 €	867 €
100	80	200	410 €	479 €	547 €	684 €	433 €	490 €	577 €
	150	300	569 €	664 €	758 €	948 €	565 €	640 €	753 €
	190	380	744 €	868 €	992 €	1.240 €	711 €	806 €	948 €
125	80	200	433 €	505 €	577 €	721 €	452 €	512 €	602 €
	150	300	619 €	722 €	826 €	1.032 €	606 €	687 €	808 €
	195	380	829 €	967 €	1.106 €	1.382 €	782 €	886 €	1.042 €
150	80	200	697 €	796 €	845 €	995 €	536 €	607 €	714 €
	120	260	1.015 €	1.067 €	1.131 €	1.324 €	714 €	809 €	952 €
	195	380	1.541 €	1.622 €	1.724 €	2.028 €	1.095 €	1.241 €	1.460 €

Required configuration - please fill in the changes in the grey gaps						
Standard-Type	Material	Interface	Groove	Width	Height	Length

Option Contour round		<table> <tr> <th>a</th><th>b</th><th>l</th><th>Screws [M]</th></tr> <tr> <td></td><td></td><td></td><td></td></tr> </table>	a	b	l	Screws [M]				
a	b	l	Screws [M]							
Option Contour straight		Customer Specific Label (max. 15 letters/numbers)								

Customer No.	
Customer Name	
Contact	

Inquiry		Order	
---------	--	-------	--

1 Set including x pieces	
order volume [set]	
Price [set]	

Signature	
-----------	--

Standard-Type	B	H	L	Interface	Material	Nut width	Screws	a	b	I	B	B1	H	L
SWB-SM 400	330	85	155	3/32" x 90°	16Mncr5	25,5	M20	min. 21	min. 34	-	330-500	150-300	40-150	max · 195
SWB-SA 400	330	98	160		16Mncr5	25,5	M20	min. 21	min. 34	-				
SFA-SM 400	330	85	160	SFA 400	AlZnMgCu1,5	18/30	M16	-	60	min	240-330	120-200	40-150	max · 195
SFA-SA 400	330	90	160		AlZnMgCu1,5	18/30	M16	-	60	. 40				
SWB-SM 315	240	70	110	1/16" x 90°	16Mncr5	21	M16	min. 17	min. 27	-	240-330	120-200	40-150	max · 195
SWB-SA 315	240	78	117	1/16" x 90°	16Mncr5	21	M16	min. 17	min. 27	-				
KMWB-SM 300	240	70	110	1,5 mm x 60°	16Mncr5	18	M14	min. 16	min. 25	-	240-330	120-200	40-150	max · 195
KMWB-SM 301	240	70	110	1,5 mm x 60°	16Mncr5	21	M16	min. 17	min. 27	-				
KMWB-SA 300	240	78	117	1,5 mm x 60°	AlZnMgCu1,5	18	M14	min. 16	min. 25	-	240-330	120-200	40-150	max · 195
KMWB-SA 301	240	78	117	1,5 mm x 60°	AlZnMgCu1,5	21	M16	min. 17	min. 27	-				
SFA-SM 315	240	75	110	SFA 315	16Mncr5	12/26.	M12	-	54	min	180-240	70-140	40-150	max · 150
SFA-SA 315	240	75	117		AlZnMgCu1,5	12/26.	M12	-	54	. 40				
SWB-SA 251	180	100	87	1/16" x 90°	AlZnMgCu1,5	21	M16	min. 17	min. 27	-	180-240	70-140	40-150	max · 150
KMWB-SM 251	180	80	80	1,5 mm x 60°	16Mncr5	16	M12	min. 14	min. 21	-				
KMWB-SA 251	180	80	87	1,5 mm x 60°	AlZnMgCu1,5	16	M12	min. 14	min. 21	-	180-240	70-140	40-150	max · 150
SWB-SM 250/21	180	70	80	1/16" x 90°	16Mncr5	21	M16	min. 16	min. 27	-				
SWB-SA 250/21	180	78	87	1/16" x 90°	AlZnMgCu1,5	21	M16	min. 16	min. 28	-	180-240	70-140	40-150	max · 150
SWB-SM 250/17	180	60	79	1/16" x 90°	16Mncr5	17	M12	min. 14	min. 21	-				
KMWB-SM 250	180	60	80	1,5 mm x 60°	16Mncr5	16	M12	min. 14	min. 21	-	180-240	70-140	40-150	max · 150
KMWB-SA 250	180	58	87	1,5 mm x 60°	AlZnMgCu1,5	16	M12	min. 14	min. 21	-				
SFA-SM 250	180	60	90	SFA 250	16Mncr5	12/20.	M12	-	40	min	140-180	50-110	40-150	max · 125
SFA-SM 251	180	80	90		16Mncr5	12/20.	M12	-	40	min				
SFA-SA 250	180	58	87		AlZnMgCu1,5	12/20.	M12	-	40	. 40				
SFA-SA 251	180	80	87		AlZnMgCu1,5	12/20.	M12	-	40	. 40				
KMWB-SM 211	140	80	70	1,5 mm x 60°	16Mncr5	14	M12	min. 14	min. 21	-	140-180	50-110	40-150	max · 125
KMWB-SA 211	140	80	72	1,5 mm x 60°	AlZnMgCu1,5	14	M12	min. 14	min. 21	-				
KMWB-SM 210	140	60	70	1,5 mm x 60°	16Mncr5	14	M12	min. 14	min. 21	-				
KMWB-SA 210	140	58	72	1,5 mm x 60°	AlZnMgCu1,5	14	M12	min. 14	min. 21	-				
SWB-SM 201	140	75	69	1/16" x 90°	16Mncr5	17	M12	min. 14	min. 21	-	140-180	50-110	40-150	max · 125
SWB-SA 201	140	75	72	1/16" x 90°	AlZnMgCu1,5	17	M12	min. 14	min. 21	-				
SWB-SM 200	140	60	69	1/16" x 90°	16Mncr5	17	M12	min. 14	min. 21	-				
SWB-SA 200	140	58	72	1/16" x 90°	16Mncr6	17	M12	min. 14	min. 21	-				
FR-SM 200	140	60	70	1/16" x 90°	16Mncr5	17	M12	min. 14	min. 21	-	140-180	50-110	40-150	max · 125
FR-SA 200	140	58	72	1/16" x 90°	16Mncr6	17	M12	min. 14	min. 21	-				
SFA-SM 201	140	80	70	SFA 200	16Mncr5	10/20.	M8	-	40	min				
SFA-SM 200	140	60	70		16Mncr5	10/20.	M8	-	40	min				
SFA-SA 201	140	80	72		AlZnMgCu1,5	10/20.	M8	-	40	. 30				
SFA-SA 200	140	58	72		AlZnMgCu1,5	10/20.	M8	-	40	. 30				
SWB-SM 165	120	60	59	1/16" x 90°	16Mncr5	14	M10	min. 13	min. 19	-	120 - 140	40 - 100	40-150	max · 100
SWB-SA 165	120	58	59	1/16" x 90°	AlZnMgCu1,5	14	M10	min. 13	min. 19	-				
SWB-SM 160	120	60	59	1/16" x 90°	16Mncr5	17	M8	min. 12	min. 16	-				
SWB-SA 160	120	58	59	1/16" x 90°	AlZnMgCu1,5	17	M8	min. 12	min. 16	-				
FR-SM 160	120	60	60	1/16" x 90°	16Mncr5	12	M8	min. 12	min. 16	-	120 - 140	40 - 100	40-150	max · 100
FR-SA 160	120	58	59	1/16" x 90°	AlZnMgCu1,5	12	M8	min. 12	min. 16	-				
KMWB-SM 165	119	50	60	1,5 mm x 60°	16Mncr5	12	M10	min. 13	min. 19	-				
KMWB-SA 165	120	58	59	1,5 mm x 60°	AlZnMgCu1,5	12	M10	min. 13	min. 19	-				
SFA-SM 160	120	50	60	SFA 160	16Mncr5	8/18.	M8	-	20	min	100-140	35-80	40-90	max · 70
SFA-SA 160	120	50	59		AlZnMgCu1,5	8/18.	M8	-	20	. 20				
FR-SM 130	100	40	50	1/16" x 90°	16Mncr5	10	M6	min. 15	min. 12	-	100-140	35-80	40-90	max · 70
FR-SA 130	100	48	47	1/16" x 90°	AlZnMgCu1,5	10	M6	min. 15	min. 12	-				