



2 weeks leadtime max.

Sonderbacken@de.schunk.com

valid until 31.12.2021



Soft top jaws									
Width up to [mm]	Height up to [mm]	Length up to [mm]	Price 3 p. set with order volume of:				Price 2 p. set with order volume of:		
			from 5 Sets 15 Pieces	from 3 Sets 9 Pieces	from 2 Sets 6 Pieces	from 1 Set 3 Pieces	from 5 Sets 10 Pieces	from 2 Sets 4 Pieces	from 1 Set 2 Pieces
			-40%	-30%	-20%	0%	-30%	-20%	0%
30	75	75	305 €	356 €	406 €	508 €	318 €	363 €	454 €
	100	100	313 €	365 €	417 €	521 €	324 €	370 €	463 €
	150	150	346 €	404 €	462 €	577 €	351 €	402 €	502 €
50	100	100	326 €	381 €	435 €	544 €	335 €	383 €	479 €
	150	180	370 €	432 €	494 €	617 €	370 €	422 €	528 €
	230	280	435 €	508 €	580 €	725 €	420 €	480 €	600 €
75	100	100	342 €	399 €	456 €	570 €	347 €	396 €	495 €
	150	180	400 €	466 €	533 €	666 €	393 €	449 €	561 €
	230	280	505 €	589 €	673 €	841 €	475 €	542 €	678 €
90	100	100	354 €	413 €	472 €	590 €	357 €	408 €	510 €
	150	280	425 €	496 €	566 €	708 €	412 €	471 €	589 €
	195	280	628 €	733 €	838 €	1.047 €	571 €	653 €	816 €
	240	280	758 €	884 €	1.010 €	1.263 €	685 €	783 €	979 €
120	100	100	379 €	442 €	505 €	631 €	377 €	430 €	538 €
	150	180	542 €	632 €	722 €	903 €	503 €	575 €	719 €
	195	280	696 €	812 €	928 €	1.160 €	623 €	712 €	890 €
	240	280	844 €	984 €	1.125 €	1.406 €	738 €	843 €	1.054 €


Required configuration - please fill in the changes in the grey gaps

Standard-Type	Material	Interface	Groove	Width	Height	Length

Option pointed

a1

a1



a	b	l	Screws [M]

Option weight reduced

ABSX


ABST

GWSX

GWSW

ABSX / ABST

GWSX / GWSW



Customer Specific Label
(max. 15 letters/numbers)

Inquiry

Order

Customer No.	
Customer Name	
Contact	

1 Set including x pieces

order volume [set]

Price [set]

Signature

Standard-Type	B	H	L	Interface	Material	Nut width	Screws	a	b	I	B	H	L		
SP-WB 800	75	90	300	3/32" x 90°	16Mncr5	30	M24	min. 22	min. 41	-	50-120	50-250	max. 280		
SP-WB 630	75	90	240			25,5	M18	min. 18	min. 31						
SP-WB 500	60	100	195					min. 18	min. 31						
SP-WB 400	60	100	155												
SWB 400	60	90	155		M20	min. 20	min. 34								
CWB 400	60	80	140												
SWB-AL 400	60	100	155					AlZnMgCu1,5							
KM-WB 211	80	80	195	3,0 mm x 60°	16MnCr5	25	M20	min. 20	min. 34						
KM-WB 213	75	115	180			25									
KM-WB 214	75	155	180			25									
KM-WB 160	60	80	150			25									
KM-WB 155	60	120	165	1,5 mm x 60°	16Mncr5	22	M20	min. 20	min. 34					Only one value over 195 possible.	
KM-WB 153	60	80	165	1,5 mm x 60°	16Mncr5	22	M20	min. 20	min. 34						
KM-WB 151	60	80	156	1,5 mm x 60°	16Mncr5	22	M20	min. 20	min. 34						
KM-WBL 150	60	60	185	1,5 mm x 60°	16Mncr5	22	M20	min. 20	min. 34						
KM-WBAL 150	60	80	145	1,5 mm x 60°	AlZnMgCu1,5	22	M20	min. 20	min. 34						
SFA 1000	76	150	350	SFA 1000	16Mncr5	24/40	M20	-	82	min. 40					
SFA-AL 1000	80	155	350		AlZnMgCu1,5										
SFA 630	65	118	260	SFA 630	16Mncr5										
SFA-AL 630	65	118	260		AlZnMgCu1,5										
WA-RN 800	60	100	210	WA-RN 800	16Mncr5	12,72/19,02	M20		76,2	min. 50					
WA-RN 500 / 630	50	80	140	WA-RN 500/630	16Mncr5										
SFA 400	50	80	180	SFA 400	16Mncr5					18/30				M16	60
SFA-AL 400	50	80	180		AlZnMgCu1,5										
SWB-FR 315	50	60	105	1/16" x 90°	16Mncr5	21	M16	min. 16	min. 27	-	40-120	40-195	max.250		
SWBL 315	50	50	140	1/16" x 90°	16Mncr5	21	M16	min. 16	min. 27						
SWBL 250-21	50	50	120	1/16" x 90°	16Mncr5	21	M16	min.16	min. 27						
CWB 251	50	60	95	1/16" x 90°	16Mncr5	21	M16	min. 16	min. 27						
SWB 250	50	80	120	1/16" x 90°	16Mncr5	21	M16	min. 16	min. 27						
SWB-AI 250	50	80	120	1/16" x 90°	AlZnMgCu1,5	21	M16	min. 16	min. 27						
KM-WB 128	50	80	129	1,5 mm x 60°	16Mncr5	21	M16	min. 16	min. 27						
KM-WB 127	50	100	140	1,5 mm x 60°	16Mncr5	21	M16	min. 16	min. 27						
KM-WB 126	50	60	129	1,5 mm x 60°	16Mncr5	21	M16	min. 16	min. 27						
KM-WB 125	50	120	130	1,5 mm x 60°	16Mncr5	21	M16	min. 16	min. 27						
KM-WBL 121	50	50	145	1,5 mm x 60°	16Mncr5	21	M16	min. 16	min. 27						
KM-WBAL 121	50	80	130	1,5 mm x 60°	16Mncr5	21	M16	min. 16	min. 27						
WA-RN 350 / 400	50	80	137	WA-RN 350 / 400	16Mncr5	12,72/19,02	M16	-	76,2	min. 40				40-160	
SFA 315	35	60	145	SFA 315	16Mncr5	12/26	M12		54						
SFA AI 315	40	60	145		AlZnMgCu1,5										
SWB-FR 250	40	60	90	1/16" x 90°	16MnCr5	17	M12	min. 12	min. 21	-	30-100	30-160	max. 200		
SWB-FR 200	40	60	70	1/16" x 90°	16Mncr5	17	M12	min. 12	min. 21						
FR-AL 200	40	60	90	1/16" x 90°	AlZnMgCu1,5	17	M12	min. 12	min. 21						
SWB-AL 200	40	60	90	1/16" x 90°	AlZnMgCu1,5	17	M12	min. 12	min. 21						
CWB 200	40	40	90	1/16" x 90°	16Mncr5	17	M12	min. 12	min. 21						
SWB 200	40	60	90	1/16" x 90°	16Mncr5	17	M12	min. 12	min. 21						
SWBL 200	35	40	98	1/16" x 90°	16Mncr5	17	M12	min. 12	min. 21						
SWB-FF 201	40	80	90	1/16" x 90°	16Mncr5	17	M14	min. 14	min. 21						
CWB 160	35	40	70	1/16" x 90°	16Mncr5	17	M12	min. 12	min. 21						
SWB 160	40	60	160	1/16" x 90°	16Mncr5	17	M12	min. 12	min. 21						
SWBL 160	35	40	78	1/16" x 90°	16Mncr5	17	M12	min. 12	min. 21						
SWB-AL 160	40	60	70	1/16" x 90°	AlZnMgCu1,5	17	M12	min. 12	min. 21						
SWB FF 160	35	40	72	1/16" x 90°	16Mncr5	14	M12	min. 12	min. 21						
SWB-FB 237	35	60	90	1/16" x 90°	16Mncr5	12	M12	min. 12	min. 21						
SWB-FBL 237	35	60	95	1/16" x 90°	16Mncr5	12	M12	min. 12	min. 21						
SWB-FB 235	30	55	84	1/16" x 90°	16Mncr5	12	M12	min. 12	min. 21						
FB-AL 175	30	60	84	1/16" x 90°	AlZnMgCu1,5	12	M12	min. 12	min. 21						
KM-WB 84	35	60	95	1,5 mm x 60°	16MnCr5	14	M12	min. 12	min. 21						
KM-WB 85	40	80	95	1,5 mm x 60°	16MnCr5	14	M12	min. 12	min. 21						
KM-WB 88	35	40	95	1,5 mm x 60°	16MnCr5	14	M12	min. 12	min. 21						
KM-WBAL 100	40	60	110	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WBAL 80	40	60	90	1,5 mm x 60°	16MnCr5	14	M12	min. 12	min. 21						
KM-WB 102	40	60	90	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WB 103	40	60	110	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WB 104	50	80	90	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WB 105	40	80	110	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WB 106	40	100	120	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WB 110	40	42	110	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WB 111	50	50	120	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WBL 100	40	42	125	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WBL 101	40	100	125	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WBL 103	40	60	125	1,5 mm x 60°	16MnCr5	16	M12	min. 12	min. 21						
KM-WBL 80	35	40	102	1,5 mm x 60°	16MnCr5	14	M12	min. 12	min. 21						
KM-WBL 81	40	80	102	1,5 mm x 60°	16MnCr5	14	M12	min. 12	min. 21						
KM-WBL 82	40	100	102	1,5 mm x 60°	16MnCr5	14	M12	min. 12	min. 21						
SFA 250	30	55	125	SFA 250	16MnCr5	12/20	M12	-	40	min. 30					
SFA AI 250	40	60	125		AlZnMgCu1,5										
WA-RN 315	40	60	120	WA-RN 250	16MnCr5	12,72/19,02			63,5						
WA-RN 250	35	60	103		16MnCr5										
FB-AL 140	25	50	70	1/16"" x 90°	AlZnMgCu1,5	10	M10	min. 11	min. 19			30-150			
KM-WB 61	35	60	72	1,5 mm x 60°	16Mncr5	12	M10	min. 11	min. 19						
KM-WB 66	32	32	72	1,5 mm x 60°	16Mncr5	12	M10	min. 11	min. 19						
KM-WBAL 70	35	50	72	1,5 mm x 60°	16Mncr5	12	M10	min. 11	min. 19						
KM-WBL 60	32	32	82	1,5 mm x 60°	16Mncr5	12	M10	min. 11	min. 19						
KM-WBL 62	35	60	82	1,5 mm x 60°	16Mncr5	12	M10	min. 11	min. 19						
SWB 165	35	60	68	1/16" x 90°	16Mncr5	14	M10	min. 11	min. 19						

SWB-AL 165	35	60	80	1/16" x 90°	AlZnMgCu1,5	14	M10	min. 11	min. 19		30-80	30-120	max.150
SWB-FB 232	30	45	70	1/16" x 90°	16Mncr5	10	M10	min. 11	min. 19				
SWB-FF 130	32	32	60	1/16" x 90°	16Mncr5	12	M10	min. 11	min. 19				
SWBL 165	35	40	80	1/16" x 90°	16Mncr5	14	M10	min. 11	min. 19				
FR-AL 160	30	55	70	1/16" x 90°	AlZnMgCu1,5	12	M8	min. 10	min. 16				
SP-WB 125	30	40	55	1/16" x 90°	16MnCr5	11	M8	min. 10	min. 16				
KM-WB 45	25	32	55	1,5 mm x 60°	16Mncr5	10	M8	min. 10	min. 16				
KM-WB 46	22	47	55	1,5 mm x 60°	16Mncr5	10	M8	min. 10	min. 16				
KM-WB 54	25	32	57	1,5 mm x 60°	16Mncr5	10	M8	min. 10	min. 16				
KM-WB 55	22	47	55	1,5 mm x 60°	16Mncr5	10	M8	min. 10	min. 16				
KM-WB 56	22	47	55	1,5 mm x 60°	16Mncr5	10	M8	min. 10	min. 16				
SWB 130	30	38	55	1/16" x 90°	16Mncr5	12	M8	min. 10	min. 16				
SWB-AL 130	30	40	55	1/16" x 90°	AlZnMgCu1,5	12	M8	min. 10	min. 16				
SWB-FR 110	25	32	62	1/16" x 90°	16Mncr5	10	M8	min. 10	min. 16				
SWB-FR 111	30	50	70	1/16" x 90°	16Mncr5	10	M8	min. 10	min. 16				
SWB-FR 160	30	38	55	1/16" x 90°	16Mncr5	12	M8	min. 10	min. 16				
SWB-FR 161	30	55	55	1/16" x 90°	16Mncr5	12	M8	min. 10	min. 16				
SWB-FR 162	35	40	72	1/16" x 90°	16Mncr5	12	M8	min. 10	min. 16				
FR-AL 130	25	45	53	1/16" x 90°	AlZnMgCu1,5	10	M6	min. 8	min. 12	20-90			
SWB-FR 130	25	30	55	1/16" x 90°	16Mncr5	10	M6	min. 8	min. 12				
SWB-FR 132	22	47	53	1/16" x 90°	16Mncr5	10	M6	min. 8	min. 12				
SWB-FR 133	32	32	62	1/16" x 90°	16Mncr5	10	M6	min. 8	min. 12				
KM-WB 44	20	40	48	1,5 mm x 60°	16Mncr5	8	M6	min. 8	min. 12				
SWB 110	20	40	50	1/16" x 90°	16Mncr5	8	M6	min. 8	min. 12				
SFA 200	22	55	100	SFA 200	16Mncr5	10/20	M8	-	40	min. 20	20-40	30-120	
SFA-AL 200	25	50	105	SFA 160	AlZnMgCu1,5	8/18			32				
SFA 160	20	40	85		16Mncr5								
SFA-AL 160	25	50	85	WA-RN 200	AlZnMgCu1,5	7,96/12,67			38,1 44,5				
SFA 140	20	40	69		16Mncr5								
WA-RN 125	26	38	62		16Mncr5								
WA_RN 160	30	45	74	WA-RN 200	16Mncr5	7,96/12,67	38,1 44,5						
WA-RN 200	30	50	87		16Mncr5								