



SCHUNK chuck jaws for ROTA-M flex 2+2 400

Flexible 4-jaw compensation chuck



Claw jaws

	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Material	m/set [kg]
	SZAU 250/4	1457356	21	50	55	25	M6	45	Steel	1.3



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 250/4	1457277	21	50	58	103.5	14	34	25	25	M16	Steel	4.8

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB 250/4	1457272	21	50	80	120	30	28	M16	Steel	12.4
	SWB-AL 250/4	1457305	21	50	80	120	30	28	M16	Aluminum	4.4

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NKS 3	0143107	21	26.5	10		M16	M16 x 35	150
	NKA 3	0145105	21	26.5	10	28	M16	M16 x 35	150



Technical advice and sales: Tel. +49-7133-103-2750