



SCHUNK chuck jaws for ROTA-M flex 2+2 260

Flexible 4-jaw compensation chuck



Claw jaws

	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Material	m/set [kg]
	SZAU 200/4	1457355	17	40	52	25	M6	35	Steel	1.1



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 210/4	1457276	17	40	49	84.2	12	28.7	19	19	M12	Steel	1.5

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB 200/4	1455397	17	40	60	90	25	22	M12	Steel	5.6
	SWB-AL 200/4	1457304	17	40	60	90	25	22	M12	Aluminum	2

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NKS 2	0143106	17	20.5	7.5		M12	M12 x 25	70
	NKA 2	0145104	17	20.5	7.5	22	M12	M12 x 25	70



Technical advice and sales: Tel. +49-7133-103-2750