





SCHUNK chuck jaws for FNC 400


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	m/set [kg]
	SFG 315	0157103	26	12	32		43	125		54	M12x1.5	3.1
	SFGL 315	0157123	26	12	32		43	160		54	M12x1.5	4
	SFG-V 315	0157153	26	12	32		46	125		54	M12x1.5	3.1
	STB 315-2	0156103	21		32	54	75	125			M16	9.3
	STN 315-4	0160503	21		32	45	55	110	13	28	M16	4.5


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	14 - 166	449	II	SZKA-ST 311	0182156	12	26	32	50	40	54	M12	Steel	2.2

Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	92 - 244	436	I	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Steel	3.9
	197 - 353	436	I	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Steel	2.7

Claw jaws for O.D. clamping



	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	200 - 355	444	I	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Steel	2.8
	44 - 181	449	II	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Steel	3.1
	135 - 290	449	II	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Steel	2.8




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for FNC 400


Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 315	0173103	12	26	240	120	320	75	69	60	110	54	54	M12	Steel	28.9
	SFA-SA 315	0174103	12	26	240	80	320	75	69	60	117	64	54	M12	Aluminum	10.8


Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	STF 315	0161103	32	81	46	129	15	Steel	5.5


Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 315	0155103	12	26	36	62	56	105	15	54	M12	Steel	3.3

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	120 - 201	364	PNK-S 400-1	0190568	99	50	3.7
	168 - 287	482	PNK-S 400-3	0190570	99	50	5.5
	225 - 344	511	PNK-S 400-5	0190572	99	50	5.4

Soft Monoblock Jaws



	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	Material	m/set [kg]
	SMB 315	0163103	32	81	46	140	Steel	7.5
	SMB-H 315	0163203	32	135	100	140	Steel	13



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for FNC 400

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 315	0153103	12	26	35	60	54		145	45	54	M12	Steel	5.6
	SFA 315-C1	0154108	12	26	40		60	54	110	30	54	M12	Steel	4.9
	SFA 315-C2	0154109	12	26	40		60	54	145	30	54	M12	Steel	6.6
	SFA 315-C3	0154110	12	26	40		100	94	145	30	54	M12	Steel	11.4
	SFA 315-C4	0154111	12	26	40		120	114	145	30	54	M12	Steel	13.8
	SFA 315-C5	0154112	12	26	40		150	144	145	30	54	M12	Steel	17.5
	SFA 315-C51	0154123	12	26	50		80	74	145	30	54	M12	Steel	11.4
	SFA 315-C6	0154113	12	26	60		60	54	110	30	54	M12	Steel	7.6
	SFA 315-C7	0154114	12	26	80		60	54	110	30	54	M12	Steel	10.3
	SFA 315-C8	0154115	12	26	80		80	74	110	30	54	M12	Steel	14.2
	SFA-AL 315	0172104	12	26	40	60	54		145	45	54	M12	Aluminum	2.4



Technical advice and sales: Tel. +49-7133-103-2750