




SCHUNK chuck jaws for KHL 200

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	52 - 81	209	HGKHA 170	0122203	12	35	50	20	M6	21	M12	Steel	1.6
	66 - 95	209	HGKHA 171	0122204	12	35	50	20	M6	21	M12	Steel	1.3
	88 - 117	209	HGKHA 172	0122205	12	35	50	20	M6	21	M12	Steel	1.3
	110 - 139	209	HGKHA 173	0122206	12	35	50	20	M6	21	M12	Steel	1.4
	132 - 161	209	HGKHA 174	0122220	12	35	50	20	M6	21	M12	Steel	1.3
	154 - 184	229	HGKHA 175	0122221	12	35	50	20	M6	21	M12	Steel	1.6
	174 - 203	249	HGKHA 176	0122225	12	35	50	20	M6	21	M12	Steel	1.9

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	D [mm]	Max. adm. tightening torque [Nm]
	TS 12	0148107	12	23.2	9	M12		100
	TM 12	0148117		19		M12	17.8	100



Technical advice and sales: Tel. +49-7133-103-2750