



SCHUNK chuck jaws for KHNC 200


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	GB 200	0159502	20	10	22	35	90	40	M8	1.21


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	10 - 35	213	II	SZKA-ST 201	0182152	10	20	22	45	37	40	M8	Steel	0.9



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	54 - 76	228	I	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Steel	1.7
	119 - 145	228	I	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Steel	1.4
	82 - 92	212	II	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Steel	1.4

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	35 - 62	229	I	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Steel	1.4
	110 - 137	229	I	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Steel	1.3
	145 - 172	234	I	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Steel	1.2
	64 - 84	213	II	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Steel	1.3

Full Grip Jaws


	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 200	0173101	10	20	140	64	200	60	56	50	70	27	40	M8	Steel	9
	SFA-SM 201	0173105	10	20	140	64	200	80	76	70	70	27	40	M8	Steel	12.5
	SFA-SA 200	0174101	10	20	140	50	200	58	54	48	72.5	32	40	M8	Aluminum	3.5
	SFA-SA 201	0174105	10	20	140	50	200	80	76	70	72.5	32	40	M8	Aluminum	4.7





Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KHNC 200

Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 200	0155101	10	20	22	42	38	71.7	10	40	M8	Steel	2.4

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 200	0153101	10	20	22	47	43		105	35	40	M8	Steel	2
	SFA 200-C1	0154100	10	20	30		55.5	51.5	100	23	40	M8	Steel	3.2
	SFA 200-C2	0154124	10	20	22		55.5	51.5	100	23	40	M8	Steel	2.2
	SFA 200-C3	0154128	10	20	40		40	36	70	23	40	M8	Steel	2.1
	SFA 200-C4	0154130	10	20	40		60	56	85	23	40	M8	Steel	4
	SFA 200-C5	0154132	10	20	40		80	76	95	23	40	M8	Steel	6.1
	SFA-AL 200	0172102	10	20	25	50	46		105	35	40	M8	Aluminum	0.9



Technical advice and sales: Tel. +49-7133-103-2750