



# SCHUNK chuck jaws for KHNC 500



## Claw jaws for I.D. clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Position of base jaws | Description | ID      | N [mm] | S [mm] | B [mm] | H [mm] | T [mm] | G  | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|-----------------------|-------------|---------|--------|--------|--------|--------|--------|----|--------|--------|----------|------------|
|  | 250 - 504         | 604                  | I                     | SZKI 411    | 0166168 | 18     | 30     | 50     | 71     | 33     | M8 | 60     | M16    | Steel    | 5.5        |
|                                                                                   | 103 - 300         | 609                  | II                    | SZKI 409    | 0166166 | 18     | 30     | 60     | 71     | 33     | M8 | 60     | M16    | Steel    | 6          |


## Claw jaws for O.D. clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Position of base jaws | Description | ID      | N [mm] | S [mm] | B [mm] | H [mm] | T [mm] | G  | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|-----------------------|-------------|---------|--------|--------|--------|--------|--------|----|--------|--------|----------|------------|
|  | 50 - 269          | 610                  | II                    | SZKA 409    | 0139170 | 18     | 30     | 50     | 71     | 33     | M8 | 60     | M16    | Steel    | 6          |
|                                                                                   | 231 - 485         | 605                  | I                     | SZKA 412    | 0139173 | 18     | 30     | 50     | 71     | 33     | M8 | 60     | M16    | Steel    | 5.1        |

## Full Grip Jaws

|                                                                                     | Description | ID      | N [mm] | S [mm] | B [mm] | B1 [mm] | Ø D [mm] | H [mm] | H1 [mm] | H2 [mm] | L [mm] | L1 [mm] | b [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|---------|----------|--------|---------|---------|--------|---------|--------|--------|----------|------------|
|   | SFA-SM 400  | 0173104 | 18     | 30     | 330    | 150     | 440      | 85     | 78      | 55      | 160    | 95      | 60     | M16    | Steel    | 55.6       |
|  | SFA-SA 400  | 0174104 | 18     | 30     | 330    | 150     | 440      | 90     | 83      | 60      | 160    | 95      | 60     | M16    | Aluminum | 22.8       |

## Hard Stepped Top Jaws



|                                                                                     | Description | ID      | N [mm] | S [mm] | B [mm] | H [mm] | H1 [mm] | L [mm] | T [mm] | b [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|---------|--------|--------|--------|--------|----------|------------|
|  | SHF 400     | 0155104 | 18     | 30     | 45     | 82     | 75      | 130    | 20     | 60     | M16    | Steel    | 6.8        |



Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for KHNC 500

## Soft Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|------------|-----------|------------|-----------|--------|----------|---------------|
|  | SFA 400     | 0153104 | 18        | 30        | 50        | 80        | 73         |            | 180       | 50         | 60        | M16    | Steel    | 13.5          |
|                                                                                   | SFA 400-C1  | 0154116 | 18        | 30        | 60        |           | 80         | 73         | 130       | 35         | 60        | M16    | Steel    | 11.8          |
|                                                                                   | SFA 400-C3  | 0154118 | 18        | 30        | 60        |           | 100        | 93         | 155       | 35         | 60        | M16    | Steel    | 21.5          |
|                                                                                   | SFA 400-C4  | 0154119 | 18        | 30        | 60        |           | 120        | 113        | 155       | 35         | 60        | M16    | Steel    | 22.4          |
|                                                                                   | SFA 400-C5  | 0154120 | 18        | 30        | 80        |           | 80         | 73         | 130       | 35         | 60        | M16    | Steel    | 16            |
|                                                                                   | SFA 400-C6  | 0154125 | 18        | 30        | 58        |           | 180        | 173        | 160       | 35         | 60        | M16    | Steel    | 35.1          |
|                                                                                   | SFA 400-C7  | 0154135 | 18        | 30        | 96        |           | 115        | 108        | 115       | 35         | 60        | M16    | Steel    | 25.9          |
|  | SFA-AL 400  | 0172105 | 18        | 30        | 50        | 80        | 73         |            | 180       | 50         | 60        | M16    | Aluminum | 5.1           |



Technical advice and sales: Tel. +49-7133-103-2750