



SCHUNK Spannbacken für 3QLC-AG 200


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (Erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 31	0112100	17	40	40	70	12	22	M12	Stahl	0.9
	SBM 32	0112101	17	40	40	90	12	22	M12	Stahl	1.1
	SBM 33	0112102	17	40	40	105	12	22	M12	Stahl	1.2
	SBM 34	0112103	17	40	60	70	12	22	M12	Stahl	1.3
	SBM 35	0112104	17	40	60	90	12	22	M12	Stahl	1.7
	SBM 36	0112105	17	40	60	105	12	22	M12	Stahl	2
	SBM 361	0112136	17	40	60	120	12	22	M12	Stahl	2.2
	SBM 3610	0112107	17	40	100	90	12	22	M12	Stahl	2.7
	SBM 3612	0112108	17	40	120	90	12	22	M12	Stahl	3.4
	SBM 3615	0112139	17	50	80	90	12	22	M12	Stahl	2.7
	SBM 368	0112106	17	40	80	90	12	22	M12	Stahl	2.3
	SBM 37	0112109	17	60	60	70	12	22	M12	Stahl	1.9
	SBM 38	0112110	17	60	60	90	12	22	M12	Stahl	2.4
	SBM 40	0112111	17	80	60	90	12	22	M12	Stahl	3.3

Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 200	0121104	17	40	49	72.5	12	18	19	19	M12	Stahl	1.6

Krallenbacken für Außenspannung


	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	45 - 105	221	SZA 16-30	0122110	17	35	50	20	M5	19	M12	Stahl	1.3
	64 - 124	224	SZA 16-31	0122111	17	35	50	20	M5	19	M12	Stahl	1.2
	86 - 146	224	SZA 16-32	0122112	17	35	50	20	M5	19	M12	Stahl	1.1
	104 - 165	225	SZA 16-33	0122113	17	40	50	20	M5	19	M12	Stahl	1.2
	126 - 187	247	SZA 16-34	0122114	17	40	50	20	M5	19	M12	Stahl	1.6
	31 - 71	224	SZA 20-14	0138195	17	35	50	25	M6	22	M12	Stahl	1.8
	45 - 98	224	SZA 20-15	0138196	17	35	50	25	M6	22	M12	Stahl	1.5
	74 - 128	225	SZA 20-16	0138197	17	40	50	25	M6	22	M12	Stahl	1.5
	101 - 155	226	SZA 20-17	0138198	17	40	50	25	M6	22	M12	Stahl	1.6
	131 - 186	249	SZA 20-18	0138199	17	40	50	25	M6	22	M12	Stahl	1.8
	35 - 67	240	SZA 25-6	0138176	17	35	55	25	M6	22	M12	Stahl	2.3
	56 - 98	224	SZA 25-7	0138177	17	35	55	25	M6	22	M12	Stahl	1.7
	102 - 156	228	SZA 25-8	0138178	17	40	55	25	M6	22	M12	Stahl	1.8
	136 - 191	258	SZA 25-9	0138179	17	40	55	25	M6	22	M12	Stahl	2.4




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für 3QLC-AG 200


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	62 - 122	222	SZI 16-18	0123190	17	35	50	20	M6	19	M12	Stahl	1.3
	75 - 134	221	SZI 16-19	0123191	17	40	50	20	M6	19	M12	Stahl	1.6
	95 - 155	222	SZI 16-20	0123192	17	40	50	20	M6	19	M12	Stahl	1.5
	116 - 175	225	SZI 16-21	0123193	17	40	50	20	M6	19	M12	Stahl	1.5
	61 - 107	225	SZI 20-10	0123164	17	35	50	20	M6	22	M12	Stahl	1.6
	81 - 135	226	SZI 20-11	0123165	17	40	50	20	M6	22	M12	Stahl	2
	112 - 166	225	SZI 20-12	0123166	17	40	50	20	M6	22	M12	Stahl	1.7
	61 - 101	241	SZI 25-17	0123180	17	35	55	25	M6	22	M12	Stahl	1.9
	79 - 125	226	SZI 25-18	0123181	17	40	55	25	M6	22	M12	Stahl	2.2
	134 - 189	239	SZI 25-19	0123182	17	40	55	25	M6	22	M12	Stahl	2



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	24 - 84	225	SZA-ST 16-1	0175100	17	35	40	30	19	M12	Stahl	1.2
	14 - 58	222	SZA-ST 20-1	0175101	17	35	45	35	22	M12	Stahl	1.5
	17 - 48	235	SZA-ST 25-1	0175102	17	35	45	35	22	M12	Stahl	1.8

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	53 - 88	220	PNS-Z 200-1	0190138	56	30	1.2
	70 - 90	220	PNS-Z 200-2	0190139	56	30	1.3
	83 - 119	242	PNS-Z 200-3	0190140	56	30	1.4
	113 - 149	240	PNS-Z 200-4	0190141	56	30	1.5
	54 - 71	234	PNS-Z 250-17-1	0190100	56	35	1.6
	97 - 129	247	PNS-Z 250-17-4	0190103	56	35	2.2
	115 - 132	247	PNS-Z 250-17-5	0190104	56	35	2.4

Segmentbacken



	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-SM 200	0169101	17	140	64	200	60	50	69.5	35	22	M12	Stahl	8.6
	SWB-SM 201	0169106	17	140	64	200	75	65	69.5	35	22	M12	Stahl	10.8
	SWB-SA 200	0170101	17	140	50	200	58	48	72.5	35	22	M12	Aluminium	3.4
	SWB-SA 201	0170106	17	140	50	200	75	65	72.5	35	22	M12	Aluminium	4.2





Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für 3QLC-AG 200

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 170	0112170	17	40	60	420	Stahl	7.6
	SBM-ST 171	0112171	17	40	80	420	Stahl	10.2
	SBM-ST 172	0112172	17	40	100	420	Stahl	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminium	2.8

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWBL 200	0120153	17	35	40	98	4	15	22	M12	Stahl	2.6
	CWB 200	0100006	17	40	40	90		25	22	M12	Stahl	2.7
	SWB 200	0120104	17	40	60	90		25	22	M12	Stahl	4.1
	SWB-AL 200	0168101	17	40	60	90		25	22	M12	Aluminium	1.5



Technische Beratung und Verkauf: Tel. +49-7133-103-2750