


SCHUNK chuck jaws for 3QLC/K 250

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	73 - 93	258	PNS-M 250-16-1	0160218	64	35	2
	79 - 116	278	PNS-M 250-16-2	0160219	64	35	1.9
	83 - 114	278	PNS-M 250-16-3	0160220	64	35	2.4
	131 - 169	292	PNS-M 250-16-4	0160221	64	35	2.3
	140 - 178	292	PNS-M 250-16-5	0160222	64	35	2.35



Technical advice and sales: Tel. +49-7133-103-2750