


SCHUNK Spannbacken für 3QLC-KT 160


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (Erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 31	0112100	17	40	40	70	12	22	M12	Stahl	0.9
	SBM 32	0112101	17	40	40	90	12	22	M12	Stahl	1.1
	SBM 33	0112102	17	40	40	105	12	22	M12	Stahl	1.2
	SBM 34	0112103	17	40	60	70	12	22	M12	Stahl	1.3
	SBM 35	0112104	17	40	60	90	12	22	M12	Stahl	1.7
	SBM 36	0112105	17	40	60	105	12	22	M12	Stahl	2
	SBM 361	0112136	17	40	60	120	12	22	M12	Stahl	2.2
	SBM 3610	0112107	17	40	100	90	12	22	M12	Stahl	2.7
	SBM 3612	0112108	17	40	120	90	12	22	M12	Stahl	3.4
	SBM 3615	0112139	17	50	80	90	12	22	M12	Stahl	2.7
	SBM 368	0112106	17	40	80	90	12	22	M12	Stahl	2.3
	SBM 37	0112109	17	60	60	70	12	22	M12	Stahl	1.9
	SBM 38	0112110	17	60	60	90	12	22	M12	Stahl	2.4
	SBM 40	0112111	17	80	60	90	12	22	M12	Stahl	3.3

Harte Stufenaufsatzbacken


	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 175	0121103	17	35	44	64.7	10	28	19		M12	Stahl	1.2
	SHB 200	0121104	17	40	49	72.5	12	18	19	19	M12	Stahl	1.6

Krallenbacken für Außenspannung


	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	30 - 74	190	SZA 16-30	0122110	17	35	50	20	M5	19	M12	Stahl	1.3
	47 - 93	193	SZA 16-31	0122111	17	35	50	20	M5	19	M12	Stahl	1.2
	69 - 115	193	SZA 16-32	0122112	17	35	50	20	M5	19	M12	Stahl	1.1
	87 - 133	194	SZA 16-33	0122113	17	40	50	20	M5	19	M12	Stahl	1.2
	109 - 156	216	SZA 16-34	0122114	17	40	50	20	M5	19	M12	Stahl	1.6
	40 - 68	193	SZA 20-15	0138196	17	35	50	25	M6	22	M12	Stahl	1.5
	63 - 98	194	SZA 20-16	0138197	17	40	50	25	M6	22	M12	Stahl	1.5
	92 - 125	196	SZA 20-17	0138198	17	40	50	25	M6	22	M12	Stahl	1.6
	114 - 155	219	SZA 20-18	0138199	17	40	50	25	M6	22	M12	Stahl	1.8
	56 - 67	193	SZA 25-7	0138177	17	35	55	25	M6	22	M12	Stahl	1.7
	88 - 125	197	SZA 25-8	0138178	17	40	55	25	M6	22	M12	Stahl	1.8
	128 - 160	227	SZA 25-9	0138179	17	40	55	25	M6	22	M12	Stahl	2.4

SCHUNK Spannbacken für 3QLC-KT 160



Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	51 - 91	190	SZI 16-18	0123190	17	35	50	20	M6	19	M12	Stahl	1.3
	66 - 103	190	SZI 16-19	0123191	17	40	50	20	M6	19	M12	Stahl	1.6
	79 - 124	191	SZI 16-20	0123192	17	40	50	20	M6	19	M12	Stahl	1.5
	99 - 144	193	SZI 16-21	0123193	17	40	50	20	M6	19	M12	Stahl	1.5
	76 - 91	193	SZI 20-10	0123164	17	35	50	20	M6	22	M12	Stahl	1.6
	79 - 104	195	SZI 20-11	0123165	17	40	50	20	M6	22	M12	Stahl	2
	95 - 135	194	SZI 20-12	0123166	17	40	50	20	M6	22	M12	Stahl	1.7
	79 - 95	195	SZI 25-18	0123181	17	40	55	25	M6	22	M12	Stahl	2.2
	117 - 158	208	SZI 25-19	0123182	17	40	55	25	M6	22	M12	Stahl	2



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	14 - 53	194	SZA-ST 16-1	0175100	17	35	40	30	19	M12	Stahl	1.2
	14 - 27	190	SZA-ST 20-1	0175101	17	35	45	35	22	M12	Stahl	1.5

Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-SM 160	0169100	17	120	40	160	60	50	59.5	25	22	M12	Stahl	5.7
	SWB-SA 160	0170100	17	120	40	165	58	48	59.5	22	22	M12	Aluminium	2.2

Verzahnte Stangen





	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 170	0112170	17	40	60	420	Stahl	7.6
	SBM-ST 171	0112171	17	40	80	420	Stahl	10.2
	SBM-ST 172	0112172	17	40	100	420	Stahl	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminium	2.8



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für 3QLC-KT 160

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWBL 160	0120151	17	35	40	78	4	15	22	M12	Stahl	1.9
	CWB 160	0100005	17	35	40	70		15	22	M12	Stahl	1.7
	SWB 160	0120102	17	40	60	70		15	22	M12	Stahl	3.1
	SWB-AL 160	0168100	17	40	60	70		15	22	M12	Aluminium	1.2



Technische Beratung und Verkauf: Tel. +49-7133-103-2750