



SCHUNK Spannbacken für KTNCV 160


Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Schrauben	m/Satz [kg]
	SFG 160	0157100	18	8	20	27	74	32	M8x1	0.8
	SFGK 160	0157500	18	8	20	27	64	32	M8x1	0.7
	SFG-V 160	0157150	18	8	20	29.5	74	32	M8x1	0.8



Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 160	0155100	8	18	20	36.5	32.5	63	7.5	32	M8	Stahl	0.6



Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	STF 160	0161100	20	45	24	79	7.5	Stahl	1.1

QUENTES Kunststoffbacken

	Spannbereich ØD	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. Anzugsmo- ment [Nm]	Schrauben	m/Satz [kg]
	20 - 67	TRQK 160	0150024	8	18	38	54	56	32		M8	0.5
		QUENTES 10-3	0150100							8		

Segmentbacken



	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 160	0173100	8	18	120	40	160	50	46	40	60	23	32	M8	Stahl	4.8
	SFA-SA 160	0174100	8	18	120	40	165	50	46	40	59.5	23	32	M8	Aluminium	1.8




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für KTN CV 160

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 160	0153100	8	18	20	40	36		85	25	32	M8	Stahl	1.2
	SFA 160-C1	0154121	8	18	30		55.5	51.5	85	19	32	M8	Stahl	2.7
	SFA 160-C2	0154127	8	18	35		40	36	63	19	32	M8	Stahl	1.6
	SFA 160-C3	0154131	8	18	40		60	56	70	19	32	M8	Stahl	3.3
	SFA 160-C4	0154133	8	18	40		80	76	85	19	32	M8	Stahl	5.6
	SFA-AL 160	0172100	8	18	25	50	46		85	25	32	M8	Aluminium	0.7

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	SMB 160	0163100	20	45	24	79	Stahl	1.5
	SMB-H 160	0163200	20	60	39	79	Stahl	2



Technische Beratung und Verkauf: Tel. +49-7133-103-2750