



SCHUNK chuck jaws for 3QLC-KT 250


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	18 - 58	263	SZA-ST 25-2	0175103	21	45	50	40	28	M16	Steel	2.7



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	80 - 117	268	SZI 25-34	0123183	21	50	58	25	M8	28	M16	Steel	3.5
	118 - 158	271	SZI 25-35	0123184	21	50	58	25	M8	28	M16	Steel	3.2
	162 - 204	270	SZI 25-36	0123185	21	50	58	25	M8	28	M16	Steel	3
	127 - 141	270	SZI 31-12	0123187	21	50	58	25	M8	28	M16	Steel	4.2
	175 - 214	269	SZI 31-13	0123188	21	50	58	25	M8	28	M16	Steel	3.9


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	48 - 88	261	SZA 25-37	0138180	21	50	58	25	M8	28	M16	Steel	3.3
	87 - 128	261	SZA 25-38	0138181	21	50	58	25	M8	28	M16	Steel	2.9
	137 - 178	264	SZA 25-39	0138182	21	50	58	25	M8	28	M16	Steel	2.7
	183 - 225	299	SZA 25-40	0138183	21	50	58	25	M8	28	M16	Steel	3.2
	46 - 65	271	SZA 31-10	0138184	21	50	58	25	M8	28	M16	Steel	3.4
	83 - 123	272	SZA 31-11	0138185	21	50	58	25	M8	28	M16	Steel	3.4
	148 - 189	270	SZA 31-12	0138186	21	50	58	25	M8	28	M16	Steel	3.2
	211 - 253	330	SZA 31-13	0138187	21	50	58	25	M8	28	M16	Steel	4.5

Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-SM 250-21	0169103	21	180	104	250	70	55	80	30	28	M16	Steel	14
	SWB-SM 251	0169107	21	180	104	250	100	85	80	30	28	M16	Steel	21.7
	SWB-SA 250-21	0170103	21	180	70	250	78	63	87.5	40	28	M16	Aluminum	7.3
	SWB-SA 251	0170107	21	180	70	250	100	85	87.5	40	28	M16	Aluminum	8.3

Hard Stepped Top Jaws


	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 250	0121105	21	50	58	103.5	14	34	25	25	M16	Steel	3.5




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for 3QLC-KT 250



Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a [mm]	Min. distance b [mm]	Screws	Material	m/piece [kg]
	SBM 41	0112112	21	50	60	90	15	28	M16	Steel	2.1
	SBM 42	0112113	21	50	60	105	15	28	M16	Steel	2.4
	SBM 4210	0112115	21	50	100	120	15	28	M16	Steel	5
	SBM 4212	0112116	21	50	120	120	15	28	M16	Steel	5.6
	SBM 4215	0112117	21	50	150	120	15	28	M16	Steel	7
	SBM 428	0112114	21	50	80	120	15	28	M16	Steel	3.7
	SBM 4281	0112137	21	50	80	150	15	28	M16	Steel	4.6
	SBM 43	0112118	21	60	60	90	15	28	M16	Steel	2.4
	SBM 44	0112119	21	60	60	105	15	28	M16	Steel	2.9
	SBM 45	0112120	21	60	80	90	15	28	M16	Steel	3.2
	SBM 46	0112121	21	60	80	105	15	28	M16	Steel	3.8
	SBM 47	0112122	21	60	80	120	15	28	M16	Steel	4.4
	SBM 48	0112123	21	80	60	90	15	28	M16	Steel	3.2
	SBM 498	0112125	21	80	80	120	15	28	M16	Steel	5.8

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	70 - 91	256	PNS-Z 250-21-1	0190105	64	35	1.9
	76 - 98	257	PNS-Z 250-21-2	0190106	64	35	2
	85 - 96	257	PNS-Z 250-21-3	0190107	64	35	2.1
	132 - 154	275	PNS-Z 250-21-4	0190108	64	35	2.3
	141 - 163	275	PNS-Z 250-21-5	0190109	64	35	2.3
	60 - 82	257	PNS-Z 315-1	0190110	64	35	2
	137 - 159	275	PNS-Z 315-3	0190112	64	35	2.5

Serrated bars





	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 210	0112180	21	50	60	420	Steel	9.4
	SBM-ST 211	0112181	21	50	80	420	Steel	12.7
	SBM-ST 212	0112182	21	50	120	420	Steel	19.3
	SBM-ST 213	0112183	21	80	80	420	Steel	20.4
	SBM-STA 210	0112184	21	50	80	420	Aluminum	4.6



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for 3QLC-KT 250

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWBL 250-21	0120155	21	50	50	120	4	20	28	M16	Steel	5.6
	CWB 251	0100012	21	50	60	95		15	28	M16	Steel	5.2
	SWB 250	0120105	21	50	80	120		30	28	M16	Steel	9.4
	SWB-AL 250	0168102	21	50	80	120		30	28	M16	Aluminum	3



Technical advice and sales: Tel. +49-7133-103-2750