

SCHUNK Spannbacken für NH/NHF 315


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 41	0112112	21	50	60	90	15	28	M16	Stahl	2.1
	SBM 42	0112113	21	50	60	105	15	28	M16	Stahl	2.4
	SBM 4210	0112115	21	50	100	120	15	28	M16	Stahl	5
	SBM 4212	0112116	21	50	120	120	15	28	M16	Stahl	5.6
	SBM 4215	0112117	21	50	150	120	15	28	M16	Stahl	7
	SBM 428	0112114	21	50	80	120	15	28	M16	Stahl	3.7
	SBM 4281	0112137	21	50	80	150	15	28	M16	Stahl	4.6
	SBM 43	0112118	21	60	60	90	15	28	M16	Stahl	2.4
	SBM 44	0112119	21	60	60	105	15	28	M16	Stahl	2.9
	SBM 45	0112120	21	60	80	90	15	28	M16	Stahl	3.2
	SBM 46	0112121	21	60	80	105	15	28	M16	Stahl	3.8
	SBM 47	0112122	21	60	80	120	15	28	M16	Stahl	4.4
	SBM 48	0112123	21	80	60	90	15	28	M16	Stahl	3.2
	SBM 498	0112125	21	80	80	120	15	28	M16	Stahl	5.8


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 315	0121111	21	50	58	128	14	46	30	30	M16	Stahl	4.6


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	44 - 134	334	SZA 31-10	0138184	21	50	58	25	M8	28	M16	Stahl	3.4
	92 - 191	335	SZA 31-11	0138185	21	50	58	25	M8	28	M16	Stahl	3.4
	156 - 257	333	SZA 31-12	0138186	21	50	58	25	M8	28	M16	Stahl	3.2
	220 - 315	387	SZA 31-13	0138187	21	50	58	25	M8	28	M16	Stahl	4.5

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	78 - 158	344	SZI 31-11	0123186	21	50	58	25	M8	28	M16	Stahl	4.1
	125 - 212	336	SZI 31-12	0123187	21	50	58	25	M8	28	M16	Stahl	4.2
	182 - 286	336	SZI 31-13	0123188	21	50	58	25	M8	28	M16	Stahl	3.9

Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	22 - 95	335	SZA-ST 31-1	0175104	21	45	50	40	28	M16	Stahl	3.3

SCHUNK Spannbacken für NH/NHF 315

Pendelbacken

A 3D perspective view of a mechanical component, likely a bracket or support. It features a central circular hole. Dimensions are indicated: $\varnothing SD_{max}$ for the hole diameter, B_1 and B_2 for horizontal widths, G for a small step width, H for the total height, L for the main body length, and N for the base width.

Segmentbacken

Technical drawing of a stepped shaft with dimensions: $\varnothing D$, H , B_1 , B , H_1 , N , a , b .

Verzahnte Stangen

A 3D perspective diagram of a rectangular bar. The length is labeled L , the width is labeled B , and the height is labeled h .

Weiche Aufsatzbacken

A 3D perspective diagram of a rectangular block. The length is labeled L , the width is B , and the height is H . On the top surface, there is a rectangular feature with width a and depth b . A dimension a_1 is shown at the front-left corner, and N is shown at the top-right corner.


A 3D perspective diagram of a rectangular block. The block has a length L , a width B , and a height H . On the top surface, there is a rectangular feature with a width a and a depth b . A dimension N is indicated as the distance from the front edge of the block to the front edge of the feature.

A 3D perspective diagram of a rectangular block. The block has a length L , a width B , and a height H . On the top surface, there is a rectangular feature with a width a and a depth b . The distance from the right edge of the block to the right edge of this feature is labeled N .



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NS 160	0140102	21	27	11		M16	M16 x 35	150
	NK 160	0145101	21	27	11	28	M16	M16 x 35	150

