



SCHUNK Spannbacken für 3QLK 315-88


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (Erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 120	0114420	21	50	60	130	15	30	M16	Stahl	3.1
	JBM 121	0114421	21	50	80	130	15	30	M16	Stahl	4.1
	JBM 122	0114422	21	50	120	130	15	30	M16	Stahl	6
	JBM 123	0114423	21	58	150	130	15	30	M16	Stahl	8.8
	JBM 124	0114424	21	80	80	130	15	30	M16	Stahl	6.2


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
			SZAJ 30-5	0138131	21	50	65	25	M8	30	M16	Stahl	3.8
	109 - 200	370	SZAJ 30-6	0138132	21	50	65	25	M8	30	M16	Stahl	4.1
	175 - 267	360	SZAJ 30-7	0138133	21	50	65	25	M8	30	M16	Stahl	3.4
	239 - 332	403	SZAJ 30-8	0138134	21	50	65	25	M8	30	M16	Stahl	4.8


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	80 - 169	350	SZIJ 30-13	0179128	21	50	65	25	M8	30	M16	Stahl	4.7
	139 - 231	358	SZIJ 30-14	0179129	21	50	65	25	M8	30	M16	Stahl	4.4
	203 - 296	342	SZIJ 30-15	0179130	21	50	65	25	M8	30	M16	Stahl	3.4
	254 - 347	393	SZIJ 30-16	0179131	21	50	65	25	M8	30	M16	Stahl	4.2

Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	37 - 113	339	SZAJ-ST 30-3	0175512	21	50	50	43	30	M16	Stahl	3.4

Pendelbacken



	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	76 - 111	291	PNS-M 315-21-1	0160223	68	35	2.35
	97 - 165	336	PNS-M 315-21-2	0160224	68	35	2.45
	153 - 211	334	PNS-M 315-21-3	0160225	68	35	2.6
	163 - 238	355	PNS-M 315-21-4	0160226	68	35	2.9




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für 3QLK 315-88

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 210	0114540	21	50	80	420	Stahl	12.7
	JBM-ST 211	0114541	21	60	120	420	Stahl	23.2
	JBM-STA 210	0114542	21	50	80	420	Aluminium	4.6

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	H-WB 125	0130124	21	50	60	111	25	35	M16	Stahl	6.2



Technische Beratung und Verkauf: Tel. +49-7133-103-2750