



SCHUNK chuck jaws for H0 1 MA 21

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	H-WB 151	0130115	26	60	80	156	34	50	M20	Steel	14.4

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 154	0146128	26	40	17	50	M20	M20 x 50	300



Technical advice and sales: Tel. +49-7133-103-2750