



SCHUNK chuck jaws for H0 1 MA 10

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	H-WB 102	0130103	16	40	60	110	25	30	M12	Steel	5.2

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 102	0146122	16	23	8	30	M12	M12 x 30	70



Technical advice and sales: Tel. +49-7133-103-2750