



SCHUNK Spannbacken für F 400


Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	b [mm]	Schrauben	m/Satz [kg]
	SFG 400	0157104	30	18	45		51	160	60	M16x1.5	7.2
	SFGL 400	0157124	30	18	45		51	200	60	M16x1.5	8.6
	STB 400-1	0156104	21		45	54	80	160		M16	12
	STB 400-2	0156105	25.5		45	64	82	160		M20	12.2


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 400	0155104	18	30	45	82	75	130	20	60	M16	Stahl	6.8


Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	STF 400	0161104	45	93	52	167	20	Stahl	10.8


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	249 - 387	506	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Stahl	5.1
	50 - 166	506	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Stahl	6
	131 - 267	506	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Stahl	5.1

Krallenbacken für Innenspannung


	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	268 - 406	505	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Stahl	5.5
	103 - 196	505	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Stahl	6
	156 - 286	505	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Stahl	5.5

Pendelbacken



	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	221 - 287	482	PNK-S 500-5	0190578	118	50	8.2
	251 - 351	521	PNK-S 500-7	0190580	118	50	8.4

SCHUNK Spannbacken für F 400


Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 400	0173104	18	30	330	150	440	85	78	55	160	95	60	M16	Stahl	55.6
	SFA-SA 400	0174104	18	30	330	150	440	90	83	60	160	95	60	M16	Aluminium	22.8

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 400	0153104	18	30	50	80	73		180	50	60	M16	Stahl	13.5
	SFA 400-C1	0154116	18	30	60		80	73	130	35	60	M16	Stahl	11.8
	SFA 400-C3	0154118	18	30	60		100	93	155	35	60	M16	Stahl	21.5
	SFA 400-C4	0154119	18	30	60		120	113	155	35	60	M16	Stahl	22.4
	SFA 400-C5	0154120	18	30	80		80	73	130	35	60	M16	Stahl	16
	SFA 400-C6	0154125	18	30	58		180	173	160	35	60	M16	Stahl	35.1
	SFA 400-C7	0154135	18	30	96		115	108	115	35	60	M16	Stahl	25.9
	SFA-AL 400	0172105	18	30	50	80	73		180	50	60	M16	Aluminium	5.1

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	SMB 400	0163104	45	93	53	176	Stahl	15
	SMB 500	0163105	45	130	90	176	Stahl	21.6



Technische Beratung und Verkauf: Tel. +49-7133-103-2750