



# SCHUNK Spannbacken für F 160


## Grundbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | b<br>[mm] | Schrauben | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SFG 160     | 0157100    | 18        | 8         | 20        | 27        | 74        | 32        | M8x1      | 0.8            |
|                                                                                   | SFGK 160    | 0157500    | 18        | 8         | 20        | 27        | 64        | 32        | M8x1      | 0.7            |
|                                                                                   | SFG-V 160   | 0157150    | 18        | 8         | 20        | 29.5      | 74        | 32        | M8x1      | 0.8            |


## Harte Stufenaufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHF 160     | 0155100    | 8         | 18        | 20        | 36.5      | 32.5       | 63        | 7.5       | 32        | M8        | Stahl     | 0.6            |



## Harte Stufenblockbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-----------|-----------|-----------|----------------|
|  | STF 160     | 0161100    | 20        | 45        | 24         | 79        | 7.5       | Stahl     | 1.1            |

## Krallenbacken für Außenspannung

|                                                                                     | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Grundbacken-<br>stellung | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|--------------------|-----------------------|--------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|----|-----------|-----------|-----------|----------------|
|  | 90 - 135           | 216                   | I                        | SZKA 163    | 0165146    | 8         | 18        | 40        | 40        | 20        | M6 | 32        | M8        | Stahl     | 1              |
|                                                                                     | 42 - 88            | 209                   | I                        | SZKA 169    | 0165174    | 8         | 18        | 26        | 40        | 20        | M6 | 32        | M8        | Stahl     | 1              |
|                                                                                     | 56 - 101           | 210                   | II                       | SZKA 163    | 0165146    | 8         | 18        | 40        | 40        | 20        | M6 | 32        | M8        | Stahl     | 1              |
|                                                                                     | 111 - 157          | 213                   | II                       | SZKA 168    | 0165151    | 8         | 18        | 30        | 40        | 20        | M6 | 32        | M8        | Stahl     | 1.3            |
|                                                                                     | 27 - 53            | 210                   | II                       | SZKA 169    | 0165174    | 8         | 18        | 26        | 40        | 20        | M6 | 32        | M8        | Stahl     | 1              |

## QUENTES Kunststoffbacken

|                                                                                     | Spannbereich<br>ØD | Bezeichnung  | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | b<br>[mm] | Max.<br>Anzugsmo-<br>ment<br>[Nm] | Schrauben | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|--------------------|--------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------------------------------|-----------|----------------|
|  | 20 - 67            | TRQK 160     | 0150024    | 8         | 18        | 38        | 54        | 56        | 32        |                                   | M8        | 0.5            |
|  |                    | QUENTES 10-3 | 0150100    |           |           |           |           |           |           | 8                                 |           |                |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

# SCHUNK Spannbacken für F 160

## Segmentbacken

|  | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|--|-------------|------------|-----------|-----------|-----------|------------|-------------|-----------|------------|------------|-----------|------------|-----------|-----------|-----------|----------------|
|  | SFA-SM 160  | 0173100    | 8         | 18        | 120       | 40         | 160         | 50        | 46         | 40         | 60        | 23         | 32        | M8        | Stahl     | 4.8            |
|  | SFA-SA 160  | 0174100    | 8         | 18        | 120       | 40         | 165         | 50        | 46         | 40         | 59.5      | 23         | 32        | M8        | Aluminium | 1.8            |

## Weiche Aufsatzbacken

|  | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|--|-------------|------------|-----------|-----------|-----------|-----------|------------|------------|-----------|------------|-----------|-----------|-----------|----------------|
|  | SFA 160     | 0153100    | 8         | 18        | 20        | 40        | 36         |            | 85        | 25         | 32        | M8        | Stahl     | 1.2            |
|  | SFA 160-C1  | 0154121    | 8         | 18        | 30        |           | 55.5       | 51.5       | 85        | 19         | 32        | M8        | Stahl     | 2.7            |
|  | SFA 160-C2  | 0154127    | 8         | 18        | 35        |           | 40         | 36         | 63        | 19         | 32        | M8        | Stahl     | 1.6            |
|  | SFA 160-C3  | 0154131    | 8         | 18        | 40        |           | 60         | 56         | 70        | 19         | 32        | M8        | Stahl     | 3.3            |
|  | SFA 160-C4  | 0154133    | 8         | 18        | 40        |           | 80         | 76         | 85        | 19         | 32        | M8        | Stahl     | 5.6            |
|  | SFA-AL 160  | 0172100    | 8         | 18        | 25        | 50        | 46         |            | 85        | 25         | 32        | M8        | Aluminium | 0.7            |

## Weiche Blockbacken

|  | Bezeichnung | Ident.-Nr. | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | Werkstoff | m/Satz<br>[kg] |
|--|-------------|------------|-----------|-----------|------------|-----------|-----------|----------------|
|  | SMB 160     | 0163100    | 20        | 45        | 24         | 79        | Stahl     | 1.5            |
|  | SMB-H 160   | 0163200    | 20        | 60        | 39         | 79        | Stahl     | 2              |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750