




SCHUNK Spannbacken für 2 BLN 315

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	2 SWK 315	0126104	25.5	80	80	125	28	35	M20	Stahl	10.1

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	S1 [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdreh- moment [Nm]
	NS 200	0140103	25.5		29	11		M20	M20 x 40	220
	NS 25.5-21	0140109	25.5	21	29	11		M16	M16 x 35	150
	NK 200	0145102	25.5		29	11	35	M20	M20 x 40	220



Technische Beratung und Verkauf: Tel. +49-7133-103-2750