



SCHUNK chuck jaws for H0 27 M 5

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	H-WB 44	0132143	11	25	32	46	8.5	16	M8	Steel	0.6

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 53	0146119	11	17.5	6.5	16	M8	M8 x 22	30



Technical advice and sales: Tel. +49-7133-103-2750