


SCHUNK Spannbacken für BS308


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 80	0114404	14	40	80	95	13	25	M12	Stahl	2.4
	JBM 81	0114400	14	40	40	70	13	25	M12	Stahl	0.9
	JBM 82	0114401	14	40	40	95	13	25	M12	Stahl	1.2
	JBM 83	0114402	14	40	60	70	13	25	M12	Stahl	1.3
	JBM 84	0114403	14	40	60	95	13	25	M12	Stahl	1.7
	JBM 85	0114405	14	40	100	95	13	25	M12	Stahl	2.9
	JBM 86	0114406	14	60	60	70	13	25	M12	Stahl	2
	JBM 87	0114407	14	80	60	70	13	25	M12	Stahl	2.6


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 80	0133109	14	35	51	87	12	15.5	25	25	M12	Stahl	1.85
	SHB-J 82	0133110	14	32	38	79	12	16	25	25	M12	Stahl	1.2


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	40 - 63	210	SZAJ 20-1	0138110	14	35	53	25	M6	25	M12	Stahl	1.9
	68 - 91	210	SZAJ 20-2	0138112	14	35	53	25	M6	25	M12	Stahl	1.6
	98 - 121	210	SZAJ 20-3	0138114	14	40	53	25	M6	25	M12	Stahl	1.7
	128 - 152	210	SZAJ 20-4	0138116	14	40	53	25	M6	25	M12	Stahl	1.6
	150 - 173	230	SZAJ 20-16	0138143	14	40	53	25	M6	25	M12	Stahl	1.7


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	57 - 78	213	SZIJ 20-1	0179110	14	35	53	20	M6	25	M12	Stahl	2
	85 - 108	213	SZIJ 20-2	0179111	14	40	53	20	M6	25	M12	Stahl	2.1
	115 - 138	210	SZIJ 20-3	0179113	14	40	53	20	M6	25	M12	Stahl	2.1
	145 - 168	219	SZIJ 20-4	0179114	14	40	53	20	M6	25	M12	Stahl	2



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	19 - 42	214	SZAJ-ST 20-2	0175503	14	35	45	38	25	M12	Stahl	1.8




Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KMWB-SM 210	0132701	14	140	70	200	60	50	70	30	25	M12	Stahl	8.8
	KMWB-SM 211	0132705	14	140	70	200	80	70	70	30	25	M12	Stahl	11.7
	KMWB-SA 210	0132801	14	140	50	200	58	48	72.5	35	25	M12	Aluminium	3.3
	KMWB-SA 211	0132805	14	140	50	200	80	70	72.5	35	25	M12	Aluminium	4.5


Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 140	0114520	14	40	80	420	Stahl	10.2
	JBM-ST 141	0114521	14	60	60	420	Stahl	11.2
	JBM-STA 140	0114522	14	40	80	420	Aluminium	3.7

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KM-WBL 80	0132601	14	35	40	102	4	20	25	M12	Stahl	2.7
	KM-WBL 81	0132607	14	40	80	102	4	20	25	M12	Stahl	6
	KM-WBL 82	0132615	14	40	100	102	4	20	25	M12	Stahl	7.6
	KM-WB 84	0132126	14	35	60	95		24	25	M12	Stahl	3.9
	KM-WB 85	0132127	14	40	80	95		24	25	M12	Stahl	6.1
	KM-WB 88	0132139	14	35	40	95		24	25	M12	Stahl	2.7
	KM-WBAL 80	0132522	14	40	60	90		20	25	M12	Aluminium	1.5

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NJ 82	0146131	14	20.5	8.5	25	M12	M12 x 30	70

