



SCHUNK chuck jaws for HJ24

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WB 211	0132114	25	80	80	195	50	60	M20	Steel	26.3
	KM-WB 213	0132155	25	75	115	180	50	60	M20	Steel	31.7
	KM-WB 214	0132200	25	75	155	180	50	60	M20	Steel	42.9

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 211	0146106	25	54	19	60	M20	M20 x 70	300



Technical advice and sales: Tel. +49-7133-103-2750