



SCHUNK Spannbacken für UVE160K


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (Erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 80	0114404	14	40	80	95	13	25	M12	Stahl	2.4
	JBM 81	0114400	14	40	40	70	13	25	M12	Stahl	0.9
	JBM 82	0114401	14	40	40	95	13	25	M12	Stahl	1.2
	JBM 83	0114402	14	40	60	70	13	25	M12	Stahl	1.3
	JBM 84	0114403	14	40	60	95	13	25	M12	Stahl	1.7
	JBM 85	0114405	14	40	100	95	13	25	M12	Stahl	2.9
	JBM 86	0114406	14	60	60	70	13	25	M12	Stahl	2
	JBM 87	0114407	14	80	60	70	13	25	M12	Stahl	2.6

Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	45 - 64	186	SZAJ 20-2	0138112	14	35	53	25	M6	25	M12	Stahl	1.6
	74 - 94	186	SZAJ 20-3	0138114	14	40	53	25	M6	25	M12	Stahl	1.7
	103 - 125	188	SZAJ 20-4	0138116	14	40	53	25	M6	25	M12	Stahl	1.6
	125 - 146	204	SZAJ 20-16	0138143	14	40	53	25	M6	25	M12	Stahl	1.7

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	93 - 113	187	SZIJ 20-3	0179113	14	40	53	20	M6	25	M12	Stahl	2.1
	121 - 142	197	SZIJ 20-4	0179114	14	40	53	20	M6	25	M12	Stahl	2



Technische Beratung und Verkauf: Tel. +49-7133-103-2750