



SCHUNK chuck jaws for UVE250K


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	31 - 62	259	SZAJ-ST 25-3	0175508	16	40	50	44	30	M12	Steel	2.5


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	62 - 101	266	SZIJ 25-1	0179116	16	40	58	25	M6	30	M12	Steel	2.7
	94 - 141	266	SZIJ 25-2	0179118	16	40	58	25	M6	30	M12	Steel	2.8
	121 - 179	261	SZIJ 25-3	0179120	16	40	58	25	M6	30	M12	Steel	2.4
	155 - 213	271	SZIJ 25-4	0179121	16	40	58	25	M6	30	M12	Steel	2.2

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	40 - 107	256	SZAJ 20-5	0138120	16	35	53	25	M6	25	M12	Steel	1.8
	67 - 135	257	SZAJ 20-6	0138125	16	35	53	25	M6	25	M12	Steel	1.6
	98 - 165	257	SZAJ 20-7	0138122	16	40	53	25	M6	25	M12	Steel	1.7
	128 - 195	258	SZAJ 20-8	0138127	16	40	53	25	M6	25	M12	Steel	1.6
	39 - 83	262	SZAJ 25-1	0138117	16	40	58	25	M6	30	M12	Steel	2.9
	68 - 125	264	SZAJ 25-2	0138119	16	40	58	25	M6	30	M12	Steel	2.3
	112 - 169	268	SZAJ 25-3	0138121	16	40	58	25	M6	30	M12	Steel	2.1
	157 - 215	282	SZAJ 25-4	0138123	16	40	58	25	M6	30	M12	Steel	2.3
	191 - 250	314	SZAJ 25-15	0138118	16	40	58	25	M6	30	M12	Steel	2.8

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	52 - 93	258	PNS-M 250-16-1	0160218	64	35	2
	63 - 107	267	PNS-M 250-16-2	0160219	64	35	1.9
	85 - 105	267	PNS-M 250-16-3	0160220	64	35	2.4
	110 - 159	281	PNS-M 250-16-4	0160221	64	35	2.3
	119 - 168	281	PNS-M 250-16-5	0160222	64	35	2.35



Technical advice and sales: Tel. +49-7133-103-2750