



SCHUNK chuck jaws for UVE160K


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	93 - 113	187	SZIJ 20-3	0179113	14	40	53	20	M6	25	M12	Steel	2.1
	121 - 142	197	SZIJ 20-4	0179114	14	40	53	20	M6	25	M12	Steel	2

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	45 - 64	186	SZAJ 20-2	0138112	14	35	53	25	M6	25	M12	Steel	1.6
	74 - 94	186	SZAJ 20-3	0138114	14	40	53	25	M6	25	M12	Steel	1.7
	103 - 125	188	SZAJ 20-4	0138116	14	40	53	25	M6	25	M12	Steel	1.6
	125 - 146	204	SZAJ 20-16	0138143	14	40	53	25	M6	25	M12	Steel	1.7

Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a [mm]	Min. distance b [mm]	Screws	Material	m/piece [kg]
	JBM 80	0114404	14	40	80	95	13	25	M12	Steel	2.4
	JBM 81	0114400	14	40	40	70	13	25	M12	Steel	0.9
	JBM 82	0114401	14	40	40	95	13	25	M12	Steel	1.2
	JBM 83	0114402	14	40	60	70	13	25	M12	Steel	1.3
	JBM 84	0114403	14	40	60	95	13	25	M12	Steel	1.7
	JBM 85	0114405	14	40	100	95	13	25	M12	Steel	2.9
	JBM 86	0114406	14	60	60	70	13	25	M12	Steel	2
	JBM 87	0114407	14	80	60	70	13	25	M12	Steel	2.6



Technical advice and sales: Tel. +49-7133-103-2750