



SCHUNK Spannbacken für MH 210


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 100	0114412	16	40	80	120	13	30	M12	Stahl	3
	JBM 101	0114410	16	40	60	90	13	30	M12	Stahl	1.6
	JBM 102	0114411	16	40	60	110	13	30	M12	Stahl	2.1
	JBM 103	0114413	16	40	100	110	13	30	M12	Stahl	3.4
	JBM 104	0114414	16	50	120	110	13	30	M12	Stahl	5
	JBM 105	0114415	16	60	60	95	13	30	M12	Stahl	2.7
	JBM 106	0114416	16	60	90	95	13	30	M12	Stahl	4
	JBM 107	0114417	16	80	60	95	13	30	M12	Stahl	3.5


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 100	0133111	16	40	54	101.5	13	25.5	30	30	M12	Stahl	2.8


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	42 - 83	260	SZAJ 25-1	0138117	16	40	58	25	M6	30	M12	Stahl	2.9
	83 - 125	260	SZAJ 25-2	0138119	16	40	58	25	M6	30	M12	Stahl	2.3
	127 - 169	264	SZAJ 25-3	0138121	16	40	58	25	M6	30	M12	Stahl	2.1
	172 - 214	280	SZAJ 25-4	0138123	16	40	58	25	M6	30	M12	Stahl	2.3
	207 - 249	312	SZAJ 25-15	0138118	16	40	58	25	M6	30	M12	Stahl	2.8

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	60 - 99	261	SZIJ 25-1	0179116	16	40	58	25	M6	30	M12	Stahl	2.7
	98 - 140	261	SZIJ 25-2	0179118	16	40	58	25	M6	30	M12	Stahl	2.8
	135 - 177	257	SZIJ 25-3	0179120	16	40	58	25	M6	30	M12	Stahl	2.4
	169 - 211	267	SZIJ 25-4	0179121	16	40	58	25	M6	30	M12	Stahl	2.2




Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	20 - 61	260	SZAJ-ST 25-3	0175508	16	40	50	44	30	M12	Stahl	2.5



Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 160	0114530	16	40	80	420	Stahl	10.2
	JBM-ST 161	0114531	16	40	120	420	Stahl	15.4
	JBM-ST 162	0114532	16	60	60	420	Stahl	11.4
	JBM-STA 160	0114533	16	40	80	420	Aluminium	3.7

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KM-WBL 100	0132602	16	40	42	125	4	30	30	M12	Stahl	4.1
	KM-WBL 101	0132608	16	40	100	125	4	30	30	M12	Stahl	9.8
	KM-WBL 103	0132609	16	40	60	125	4	30	30	M12	Stahl	5.7
	KM-WB 102	0132104	16	40	60	90		15	30	M12	Stahl	4.3
	KM-WB 103	0132105	16	40	60	110		30	30	M12	Stahl	5.2
	KM-WB 104	0132106	16	50	80	90		15	30	M12	Stahl	7.3
	KM-WB 105	0132129	16	40	80	110		30	30	M12	Stahl	7.2
	KM-WB 106	0132152	16	40	100	120		30	30	M12	Stahl	9.9
	KM-WB 110	0132140	16	40	42	110		30	30	M12	Stahl	3.8
	KM-WB 111	0132147	16	50	50	120		30	30	M12	Stahl	6.2
	KM-WBAL 100	0132523	16	40	60	110		25	30	M12	Aluminium	1.9

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NJ 103	0146132	16	21.5	8.5	30	M12	M12 x 30	70
	NJ 103 gesägt/sawn	0146002	16	21.5	8.5		M12	M12 x 30	70



Technische Beratung und Verkauf: Tel. +49-7133-103-2750