


# SCHUNK chuck jaws for MH 206



## Claw jaws For bar clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Description  | ID      | N [mm] | B [mm] | H [mm] | T [mm] | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|--------------|---------|--------|--------|--------|--------|--------|--------|----------|------------|
|  | 12 - 33           | 172                  | SZAJ-ST 16-2 | 0175501 | 12     | 30     | 40     | 34     | 20     | M10    | Steel    | 1.1        |


## Claw jaws for O.D. clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Description | ID      | N [mm] | B [mm] | H [mm] | T [mm] | G  | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|-------------|---------|--------|--------|--------|--------|----|--------|--------|----------|------------|
|  | 41 - 67           | 172                  | SZAJ 16-7   | 0176101 | 12     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1          |
|                                                                                   | 57 - 83           | 172                  | SZAJ 16-8   | 0176102 | 12     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1.1        |
|                                                                                   | 71 - 97           | 172                  | SZAJ 16-9   | 0176103 | 12     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1.1        |
|                                                                                   | 87 - 113          | 172                  | SZAJ 16-10  | 0176104 | 12     | 40     | 47     | 20     | M6 | 20     | M10    | Steel    | 1.2        |


## Full Grip Jaws

|                                                                                     | Description | ID      | N [mm] | B [mm] | B1 [mm] | Ø D [mm] | H [mm] | H1 [mm] | L [mm] | a [mm] | b [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|---------|----------|--------|---------|--------|--------|--------|--------|----------|------------|
|   | KMWB-SM 165 | 0132700 | 12     | 120    | 50      | 160      | 50     | 40      | 60     | 25     | 20     | M10    | Steel    | 4.9        |
|  | KMWB-SA 165 | 0132800 | 12     | 120    | 40      | 165      | 58     | 48      | 59.5   | 25     | 20     | M10    | Aluminum | 2.2        |

## Hard Stepped Top Jaws

|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | T [mm] | a [mm] | b [mm] | c [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|----------|------------|
|  | SHB-J 60    | 0133100 | 12     | 28     | 36     | 67     | 12     | 14     | 20     | 20     | M10    | Steel    | 0.8        |

## Jaw blanks


|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | Min. distance a (jaw tip up to first hole) [mm] | Min. distance b (first up to second hole) [mm] | Screws | Material | m/piece [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|-------------------------------------------------|------------------------------------------------|--------|----------|--------------|
|  | SBMJ 70     | 0132150 | 12     | 35     | 60     | 80     | 12                                              | 20                                             | M10    | Steel    | 1.3          |





Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for MH 206




## QUENTES fiberglass jaws

|                                                                                   | Clamping range ØD | Description  | ID      | N [mm] | B [mm] | H [mm] | L [mm] | b [mm] | Max. tightening torque [Nm] | Screws | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|--------------|---------|--------|--------|--------|--------|--------|-----------------------------|--------|------------|
|  | 20 - 34           | TRQJ 160-1   | 0150022 | 12     | 40     | 55     | 65     | 20     |                             | M10    | 0.6        |
|  |                   | QUINTES 10-3 | 0150100 |        |        |        |        |        | 8                           |        |            |

## Serrated bars

|                                                                                    | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | Material | m/piece [kg] |
|------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|----------|--------------|
|   | JBM-ST 120  | 0114510 | 12     | 35     | 60     | 420    | Steel    | 6.7          |
|  | JBM-STA 120 | 0114511 | 12     | 40     | 60     | 420    | Aluminum | 2.8          |

## Soft Top Jaws


|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | a1 [mm] | a [mm] | b [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|---------|--------|--------|--------|----------|------------|
|  | KM-WBL 60   | 0132600 | 12     | 32     | 32     | 82     | 4       | 15     | 20     | M10    | Steel    | 1.5        |
|                                                                                     | KM-WBL 62   | 0132606 | 12     | 35     | 60     | 82     | 4       | 15     | 20     | M10    | Steel    | 3.6        |
|  | KM-WB 61    | 0130128 | 12     | 35     | 60     | 72     |         | 15     | 20     | M10    | Steel    | 2.9        |
|                                                                                     | KM-WB 66    | 0132138 | 12     | 32     | 32     | 72     |         | 15     | 20     | M10    | Steel    | 1.4        |
|  | KM-WBAL 70  | 0132521 | 12     | 35     | 50     | 72     |         | 15     | 20     | M10    | Aluminum | 0.9        |



Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for MH 206

## T-nut

|                                                                                   | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Cyl.-screw | Max. adm.<br>tightening<br>torque<br>[Nm] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|-----|------------|-------------------------------------------|
|  | NJ 62       | 0146133 | 12        | 18.5      | 7.5        | 20        | M10 | M10 x 25   | 50                                        |



Technical advice and sales: Tel. +49-7133-103-2750