




SCHUNK chuck jaws for HC 05


Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a (jaw tip up to first hole) [mm]	Min. distance b (first up to second hole) [mm]	Screws	Material	m/piece [kg]
	SBMJ 50	0132149	10	22	47	55	8	14	M8	Steel	0.4


Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-ST 100	0114500	10	32	32	420	Steel	3.1
	JBM-STA 100	0114501	10	30	40	420	Aluminum	1.3

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	KM-WB 56	0132137	10	22	47	55	4	10	19	M8	Steel	1

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 51	0146117	10	18	5.5	19	M8	M8 x 22	30



Technical advice and sales: Tel. +49-7133-103-2750