




SCHUNK chuck jaws for HSF 12


Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a (jaw tip up to first hole) [mm]	Min. distance b (first up to second hole) [mm]	Screws	Material	m/piece [kg]
	JBM 120	0114420	21	50	60	130	15	30	M16	Steel	3.1
	JBM 121	0114421	21	50	80	130	15	30	M16	Steel	4.1
	JBM 122	0114422	21	50	120	130	15	30	M16	Steel	6
	JBM 123	0114423	21	58	150	130	15	30	M16	Steel	8.8
	JBM 124	0114424	21	80	80	130	15	30	M16	Steel	6.2

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-ST 210	0114540	21	50	80	420	Steel	12.7
	JBM-ST 211	0114541	21	60	120	420	Steel	23.2
	JBM-STA 210	0114542	21	50	80	420	Aluminum	4.6

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 124	0146123	21	28	11.5	30	M16	M16 x 40	150



Technical advice and sales: Tel. +49-7133-103-2750