



SCHUNK chuck jaws for DURO 630


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	SFG 630	0157106	40	24	65	58	230	82	M20	17.1
	SFG 630-400	0157109	30	18	65	58	230	60	M16x1.5	16.2


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	327 - 605	745	I	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	418 - 696	797	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5
	109 - 351	802	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	165 - 442	802	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	297 - 575	798	I	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	399 - 677	798	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1
	219 - 496	799	I	SZKA 631	0139200	24	40	65	97	42	M8	82	M20	Steel	13
	379 - 657	799	I	SZKA 632	0139201	24	40	65	97	42	M8	82	M20	Steel	11.8
	65 - 321	803	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	129 - 423	803	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1
	88 - 328	802	II	SZKA 631	0139200	24	40	65	97	42	M8	82	M20	Steel	13
	212 - 489	802	II	SZKA 632	0139201	24	40	65	97	42	M8	82	M20	Steel	11.8

Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 630	0155106	24	40	65	105	97	185	30	82	M20	Steel	18

Soft Monoblock Jaws



	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	Material	m/set [kg]
	SMB 630-800	0163106	65	130	88	230	Steel	40



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for DURO 630

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 630	0153106	24	40	65	118	110		260	70	82	M20	Steel	39.6
	SFA 400-C1	0154116	18	30	60		80	73	130	35	60	M16	Steel	11.8
	SFA 400-C3	0154118	18	30	60		100	93	155	35	60	M16	Steel	21.5
	SFA 400-C4	0154119	18	30	60		120	113	155	35	60	M16	Steel	22.4
	SFA 400-C5	0154120	18	30	80		80	73	130	35	60	M16	Steel	16
	SFA 400-C6	0154125	18	30	58		180	173	160	35	60	M16	Steel	35.1
	SFA 400-C7	0154135	18	30	96		115	108	115	35	60	M16	Steel	25.9
	SFA-AL 630	0172106	24	40	65	118	110		260	70	82	M20	Aluminum	14.8



Technical advice and sales: Tel. +49-7133-103-2750