




SCHUNK chuck jaws for DURO-NC 168


Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 160	0155100	8	18	20	36.5	32.5	63	7.5	32	M8	Steel	0.6

QUENTES fiberglass jaws

	Clamping range ØD	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. tightening torque [Nm]	Screws	m/set [kg]
	20 - 85	TRQK 160	0150024	8	18	38	54	56	32		M8	0.5
		QUINTES 10-3	0150100							8		

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 140	0153098	8	18	20	40	36		69	25	32	M8	Steel	0.9
	SFA 140-C1	0154129	8	18	30		45	41	63	19	32	M8	Steel	1.7



Technical advice and sales: Tel. +49-7133-103-2750