



SCHUNK chuck jaws for HW08


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	14 - 117	37	SZAJ-ST 16-2	0175501	12	30	40	34	20	M10	Steel	1.1

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	30 - 101	38	SZAJ 16-6	0176100	12	30	47	20	M6	20	M10	Steel	1.2
	31 - 85	38	SZAJ 16-7	0176101	12	30	47	20	M6	20	M10	Steel	1
	43 - 70	41	SZAJ 16-8	0176102	12	30	47	20	M6	20	M10	Steel	1.1

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 60	0133100	12	28	36	67	12	14	20	20	M10	Steel	0.8



Technical advice and sales: Tel. +49-7133-103-2750