



# SCHUNK Spannbacken für NV40



## Harte Stufenaufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHB-J 152   | 0133106    | 22        | 60        | 75        | 144.5     | 17.5      | 66        | 50        | M20       | Stahl     | 9.8            |

## Weiche Aufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | KM-WB 160   | 0132134    | 22        | 60        | 80        | 150       | 45        | 50        | M20       | Stahl     | 13.8           |
|                                                                                   | KM-WB 211   | 0132114    | 25        | 80        | 80        | 195       | 50        | 60        | M20       | Stahl     | 26.3           |
|                                                                                   | KM-WB 213   | 0132155    | 25        | 75        | 115       | 180       | 50        | 60        | M20       | Stahl     | 31.7           |
|                                                                                   | KM-WB 214   | 0132200    | 25        | 75        | 155       | 180       | 50        | 60        | M20       | Stahl     | 42.9           |

## Nutenstein

|                                                                                     | Bezeichnung | Ident.-Nr. | S<br>[mm] | S1<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Zyl.-Schraube | Max. zul.<br>Anziehdreh-<br>moment<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|------------|-----------|------------|-----------|-----|---------------|--------------------------------------------|
|   | NJ 210      | 0146126    | 25        |            | 45        | 19         | 60        | M20 | M20 x 60      | 300                                        |
|  | NJ 213      | 0146140    | 25        | 22         | 45        | 19         | 50        | M20 | M20 x 55      | 300                                        |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750