




Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	34 - 64	213	SZAJ 20-5	0138120	16	35	53	25	M6	25	M12	Stahl	1.8
	61 - 92	214	SZAJ 20-6	0138125	16	35	53	25	M6	25	M12	Stahl	1.6
	92 - 122	214	SZAJ 20-7	0138122	16	40	53	25	M6	25	M12	Stahl	1.7
	122 - 152	215	SZAJ 20-8	0138127	16	40	53	25	M6	25	M12	Stahl	1.6
	62 - 83	221	SZAJ 25-2	0138119	16	40	58	25	M6	30	M12	Stahl	2.3
	106 - 127	225	SZAJ 25-3	0138121	16	40	58	25	M6	30	M12	Stahl	2.1
	150 - 172	239	SZAJ 25-4	0138123	16	40	58	25	M6	30	M12	Stahl	2.3
	185 - 207	270	SZAJ 25-15	0138118	16	40	58	25	M6	30	M12	Stahl	2.8

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	115 - 136	218	SZIJ 25-3	0179120	16	40	58	25	M6	30	M12	Stahl	2.4
	149 - 170	228	SZIJ 25-4	0179121	16	40	58	25	M6	30	M12	Stahl	2.2

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	45 - 64	225	PNS-M 250-16-1	0160218	64	35	2
	104 - 122	239	PNS-M 250-16-4	0160221	64	35	2.3
	113 - 125	239	PNS-M 250-16-5	0160222	64	35	2.35

