



SCHUNK chuck jaws for UVE315K


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	37 - 109	329	SZAJ-ST 30-1	0175510	18	50	50	43	30	M14	Steel	3.5


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	87 - 165	346	SZIJ 30-9	0179122	18	50	65	25	M8	30	M14	Steel	5
	147 - 227	353	SZIJ 30-10	0179124	18	50	65	25	M8	30	M14	Steel	4.6
	210 - 290	337	SZIJ 30-11	0179126	18	50	65	25	M8	30	M14	Steel	3.6
	263 - 343	389	SZIJ 30-12	0179127	18	50	65	25	M8	30	M14	Steel	4.5

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	114 - 194	333	SZAJ 25-10	0138129	18	40	58	25	M6	30	M14	Steel	2.3
	156 - 236	336	SZAJ 25-11	0138141	18	45	58	25	M6	30	M14	Steel	2.3
	204 - 284	355	SZAJ 25-12	0138142	18	45	58	25	M6	30	M14	Steel	2.5
	57 - 137	352	SZAJ 30-1	0138124	18	50	65	25	M8	30	M14	Steel	3.8
	117 - 196	364	SZAJ 30-2	0138126	18	50	65	25	M8	30	M14	Steel	4.1
	183 - 263	359	SZAJ 30-3	0138128	18	50	65	25	M8	30	M14	Steel	3.4
	248 - 328	402	SZAJ 30-4	0138130	18	50	65	25	M8	30	M14	Steel	4.8

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	83 - 112	291	PNS-M 315-18-1	0160210	68	35	2.4
	97 - 162	332	PNS-M 315-18-2	0160211	68	35	2.45
	160 - 211	334	PNS-M 315-18-3	0160212	68	35	2.65
	170 - 235	352	PNS-M 315-18-4	0160213	68	35	3



Technical advice and sales: Tel. +49-7133-103-2750