



SCHUNK chuck jaws for UPR450


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	187 - 231	462	SZIJ 38-1	0179132	22	60	85	33	M8	43	M20	Steel	9.5
	243 - 287	466	SZIJ 38-2	0179133	22	60	85	33	M8	43	M20	Steel	9.1
	298 - 343	461	SZIJ 38-3	0179134	22	60	85	33	M8	43	M20	Steel	7.6
	369 - 413	471	SZIJ 38-4	0179135	22	60	85	33	M8	43	M20	Steel	7.1
	429 - 473	522	SZIJ 38-5	0179136	22	60	85	33	M8	43	M20	Steel	8.6

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	131 - 176	464	SZAJ 38-1	0138135	22	60	85	33	M8	43	M20	Steel	10.2
	189 - 233	469	SZAJ 38-2	0138136	22	60	85	33	M8	43	M20	Steel	9
	249 - 293	469	SZAJ 38-3	0138137	22	60	85	33	M8	43	M20	Steel	7.5
	310 - 355	488	SZAJ 38-4	0138138	22	60	85	33	M8	43	M20	Steel	7.5
	370 - 415	506	SZAJ 38-5	0138139	22	60	85	33	M8	43	M20	Steel	8.2
	430 - 475	557	SZAJ 38-6	0138140	22	60	85	33	M8	43	M20	Steel	9.5

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	JBM-STA 220	0114552	22	60	100	420	Aluminum	7



Technical advice and sales: Tel. +49-7133-103-2750