



SCHUNK Spannbacken für HSL 10


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a (Backen- spitze bis erste Bohrung) [mm]	Min. Abstand b (erste bis zweite Bohrung) [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 100	0114412	16	40	80	120	13	30	M12	Stahl	3
	JBM 101	0114410	16	40	60	90	13	30	M12	Stahl	1.6
	JBM 102	0114411	16	40	60	110	13	30	M12	Stahl	2.1
	JBM 103	0114413	16	40	100	110	13	30	M12	Stahl	3.4
	JBM 104	0114414	16	50	120	110	13	30	M12	Stahl	5
	JBM 105	0114415	16	60	60	95	13	30	M12	Stahl	2.7
	JBM 106	0114416	16	60	90	95	13	30	M12	Stahl	4
	JBM 107	0114417	16	80	60	95	13	30	M12	Stahl	3.5


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 100	0133111	16	40	54	101.5	13	25.5	30	30	M12	Stahl	2.8


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	47 - 113	263	SZAJ 20-5	0138120	16	35	53	25	M6	25	M12	Stahl	1.8
	74 - 141	264	SZAJ 20-6	0138125	16	35	53	25	M6	25	M12	Stahl	1.6
	105 - 171	264	SZAJ 20-7	0138122	16	40	53	25	M6	25	M12	Stahl	1.7
	135 - 202	265	SZAJ 20-8	0138127	16	40	53	25	M6	25	M12	Stahl	1.6
	39 - 89	269	SZAJ 25-1	0138117	16	40	58	25	M6	30	M12	Stahl	2.9
	75 - 131	271	SZAJ 25-2	0138119	16	40	58	25	M6	30	M12	Stahl	2.3
	119 - 176	274	SZAJ 25-3	0138121	16	40	58	25	M6	30	M12	Stahl	2.1
	164 - 221	288	SZAJ 25-4	0138123	16	40	58	25	M6	30	M12	Stahl	2.3
	199 - 256	320	SZAJ 25-15	0138118	16	40	58	25	M6	30	M12	Stahl	2.8

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	62 - 107	273	SZIJ 25-1	0179116	16	40	58	25	M6	30	M12	Stahl	2.7
	94 - 147	273	SZIJ 25-2	0179118	16	40	58	25	M6	30	M12	Stahl	2.8
	128 - 185	268	SZIJ 25-3	0179120	16	40	58	25	M6	30	M12	Stahl	2.4
	162 - 219	277	SZIJ 25-4	0179121	16	40	58	25	M6	30	M12	Stahl	2.2


Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	31 - 68	265	SZAJ-ST 25-3	0175508	16	40	50	44	30	M12	Stahl	2.5





Technische Beratung und Verkauf: Tel. +49-7133-103-2750




Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KMWB-SM 250	0132702	16	180	100	250	60	45	80	30	30	M12	Stahl	12
	KMWB-SM 251	0132706	16	180	100	250	80	70	80	30	30	M12	Stahl	18.5
	KMWB-SA 250	0132802	16	180	70	250	58	43	87.5	40	30	M12	Aluminium	4.7
	KMWB-SA 251	0132806	16	180	70	250	80	65	87.5	40	30	M12	Aluminium	6.6

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 160	0114530	16	40	80	420	Stahl	10.2
	JBM-ST 161	0114531	16	40	120	420	Stahl	15.4
	JBM-ST 162	0114532	16	60	60	420	Stahl	11.4
	JBM-STA 160	0114533	16	40	80	420	Aluminium	3.7

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KM-WBL 100	0132602	16	40	42	125	4	30	30	M12	Stahl	4.1
	KM-WBL 101	0132608	16	40	100	125	4	30	30	M12	Stahl	9.8
	KM-WBL 103	0132609	16	40	60	125	4	30	30	M12	Stahl	5.7
	KM-WB 102	0132104	16	40	60	90		15	30	M12	Stahl	4.3
	KM-WB 103	0132105	16	40	60	110		30	30	M12	Stahl	5.2
	KM-WB 104	0132106	16	50	80	90		15	30	M12	Stahl	7.3
	KM-WB 105	0132129	16	40	80	110		30	30	M12	Stahl	7.2
	KM-WB 106	0132152	16	40	100	120		30	30	M12	Stahl	9.9
	KM-WB 110	0132140	16	40	42	110		30	30	M12	Stahl	3.8
	KM-WB 111	0132147	16	50	50	120		30	30	M12	Stahl	6.2
	KM-WBAL 100	0132523	16	40	60	110		25	30	M12	Aluminium	1.9



Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NJ 103	0146132	16	21.5	8.5	30	M12	M12 x 30	70

