



SCHUNK chuck jaws for DURO-NC 175


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	SFG 160	0157100	18	8	20	27	74	32	M8x1	0.8
	SFGK 160	0157500	18	8	20	27	64	32	M8x1	0.7
	SFG-V 160	0157150	18	8	20	29.5	74	32	M8x1	0.8



Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	10 - 66	233	II	SZKA-ST 161	0182150	8	18	22	40	30	32	M8	Steel	0.8


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	90 - 153	234	I	SZKA 163	0165146	8	18	40	40	20	M6	32	M8	Steel	1
	42 - 105	227	I	SZKA 169	0165174	8	18	26	40	20	M6	32	M8	Steel	1
	59 - 124	233	II	SZKA 163	0165146	8	18	40	40	20	M6	32	M8	Steel	1
	110 - 175	236	II	SZKA 167	0165150	8	18	30	40	20	M6	32	M8	Steel	1.3

Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 160	0173100	8	18	120	40	160	50	46	40	60	23	32	M8	Steel	4.8
	SFA-SA 160	0174100	8	18	120	40	165	50	46	40	59.5	23	32	M8	Aluminum	1.8

Hard Stepped Block Jaws


	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	STF 160	0161100	20	45	24	79	7.5	Steel	1.1





Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for DURO-NC 175


Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 160	0155100	8	18	20	36.5	32.5	63	7.5	32	M8	Steel	0.6



QUENTES fiberglass jaws

	Clamping range ØD	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. tightening torque [Nm]	Screws	m/set [kg]
	20 - 85	TRQK 160	0150024	8	18	38	54	56	32		M8	0.5
		QUENTES 10-3	0150100							8		

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	Material	m/set [kg]
	SMB 160	0163100	20	45	24	79	Steel	1.5
	SMB-H 160	0163200	20	60	39	79	Steel	2

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 160	0153100	8	18	20	40	36		85	25	32	M8	Steel	1.2
	SFA 160-C1	0154121	8	18	30		55.5	51.5	85	19	32	M8	Steel	2.7
	SFA 160-C2	0154127	8	18	35		40	36	63	19	32	M8	Steel	1.6
	SFA 160-C3	0154131	8	18	40		60	56	70	19	32	M8	Steel	3.3
	SFA 160-C4	0154133	8	18	40		80	76	85	19	32	M8	Steel	5.6
	SFA-AL 160	0172100	8	18	25	50	46		85	25	32	M8	Aluminum	0.7



Technical advice and sales: Tel. +49-7133-103-2750