



SCHUNK Spannbacken für HG-2G 500-165


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	144 - 301	522	I	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Stahl	6
	245 - 402	522	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Stahl	5.1
	55 - 194	534	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Stahl	6
	125 - 295	534	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Stahl	5.1

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	174 - 331	522	I	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Stahl	6
	264 - 421	521	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Stahl	5.5
	110 - 224	533	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Stahl	6
	158 - 314	533	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Stahl	5.5

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	108 - 195	463	PNK-G 500-2	0190625	118	50	4.4
	163 - 242	538	PNK-G 500-4	0190627	118	50	5.5
	215 - 277	471	PNK-G 500-6	0190629	118	50	5.8
	245 - 342	511	PNK-G 500-8	0190631	118	50	6.2
	307 - 468	651	PNK-G 500-10	0190633	118	50	8.3



Technische Beratung und Verkauf: Tel. +49-7133-103-2750