



# SCHUNK Spannbacken für HG 160


## Grundbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | b<br>[mm] | Schrauben | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | GBK 160     | 0159106    | 18        | 8         | 20        | 27.5      | 65        | 32        | M8        | 0.6            |
|                                                                                   | GBK-V 160   | 0159156    | 18        | 8         | 20        | 27.5      | 65        | 32        | M8        | 0.6            |



## Harte Stufenaufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHF 160     | 0155100    | 8         | 18        | 20        | 36.5      | 32.5       | 63        | 7.5       | 32        | M8        | Stahl     | 0.6            |



## Harte Stufenblockbacken

|                                                                                   | Bezeichnung       | Ident.-Nr. | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------------|------------|-----------|-----------|------------|-----------|-----------|-----------|----------------|
|  | GST 140-160<br>I  | 0162097    | 20        | 43.5      | 22         | 58        | 7         | Stahl     | 0.7            |
|                                                                                   | GST 140-160<br>II | 0162098    | 20        | 43.5      | 22         | 58        | 7         | Stahl     | 0.7            |

## QUENTES Kunststoffbacken

|                                                                                     | Spannbereich<br>ØD                                                                  | Bezeichnung  | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | b<br>[mm] | Max.<br>Anzugsmo-<br>ment<br>[Nm] | Schrauben | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------------------------------|-----------|----------------|
|  | 20 - 73                                                                             | TRQK 160     | 0150024    | 8         | 18        | 38        | 54        | 56        | 32        |                                   | M8        | 0.5            |
|                                                                                     |  | QUENTES 10-3 | 0150100    |           |           |           |           |           |           | 8                                 |           |                |

## Segmentbacken



|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|------------|-------------|-----------|------------|------------|-----------|------------|-----------|-----------|-----------|----------------|
|  | SFA-SM 160  | 0173100    | 8         | 18        | 120       | 40         | 160         | 50        | 46         | 40         | 60        | 23         | 32        | M8        | Stahl     | 4.8            |
|  | SFA-SA 160  | 0174100    | 8         | 18        | 120       | 40         | 165         | 50        | 46         | 40         | 59.5      | 23         | 32        | M8        | Aluminium | 1.8            |




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

# SCHUNK Spannbacken für HG 160

## Weiche Aufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|------------|-----------|------------|-----------|-----------|-----------|----------------|
|  | SFA 160     | 0153100    | 8         | 18        | 20        | 40        | 36         |            | 85        | 25         | 32        | M8        | Stahl     | 1.2            |
|                                                                                   | SFA 160-C1  | 0154121    | 8         | 18        | 30        |           | 55.5       | 51.5       | 85        | 19         | 32        | M8        | Stahl     | 2.7            |
|                                                                                   | SFA 160-C2  | 0154127    | 8         | 18        | 35        |           | 40         | 36         | 63        | 19         | 32        | M8        | Stahl     | 1.6            |
|                                                                                   | SFA 160-C3  | 0154131    | 8         | 18        | 40        |           | 60         | 56         | 70        | 19         | 32        | M8        | Stahl     | 3.3            |
|                                                                                   | SFA 160-C4  | 0154133    | 8         | 18        | 40        |           | 80         | 76         | 85        | 19         | 32        | M8        | Stahl     | 5.6            |
|  | SFA-AL 160  | 0172100    | 8         | 18        | 25        | 50        | 46         |            | 85        | 25         | 32        | M8        | Aluminium | 0.7            |

## Weiche Blockbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-----------|-----------|----------------|
|  | UVB 160     | 0164106    | 20        | 55.5      | 35         | 65        | Stahl     | 1.6            |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750