



SCHUNK chuck jaws for HG-2G 630-254


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	247 - 291	683	I	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	337 - 582	682	I	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5
	106 - 292	681	II	SZKI 409	0166166	18	30	60	71	33	M8	60	M16	Steel	6
	167 - 382	681	II	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	217 - 461	683	I	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	319 - 563	683	I	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1
	52 - 262	682	II	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	135 - 364	683	II	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	163 - 276	563	PNK-G 630-2	0190635	118	50	7.9
	228 - 341	603	PNK-G 630-4	0190637	118	50	8.3
	329 - 479	663	PNK-G 630-6	0190639	118	50	10.4
	397 - 532	727	PNK-G 630-8	0190641	118	50	12



Technical advice and sales: Tel. +49-7133-103-2750