





# SCHUNK chuck jaws for DURO-NCES 200


## Base Jaws

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | B1<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|--------|---------------|
|  | GBK 200     | 0159100 | 20        | 10        | 22        |            | 29.5      | 85        |           | 40        | M8     | 1             |
|                                                                                   | GBKL 200    | 0159120 | 20        | 10        | 22        |            | 29.5      | 105       |           | 40        | M8     | 1.2           |
|                                                                                   | GBK-V 200   | 0159150 | 20        | 10        | 22        |            | 29.5      | 85        |           | 40        | M8     | 1             |
|  | STB-G 200-1 | 0160655 | 17        |           | 22        | 45         | 59        | 85        |           |           | M12    | 3             |
|  | STNJ 200-5  | 0160650 | 14        |           | 22        | 40         | 47        | 95        | 10        | 25        | M12    | 2.6           |


## Claw jaws For bar clamping

|                                                                                    | Clamping<br>range ØD | Swing<br>diameter<br>SDmax | Position of<br>base jaws | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|------------------------------------------------------------------------------------|----------------------|----------------------------|--------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | 15 - 89              | 268                        | II                       | SZKA-ST 201 | 0182152 | 10        | 20        | 22        | 45        | 37        | 40        | M8     | Steel    | 0.9           |

## Claw jaws for I.D. clamping

|                                                                                     | Clamping<br>range ØD | Swing<br>diameter<br>SDmax | Position of<br>base jaws | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|----------------------|----------------------------|--------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|----|-----------|--------|----------|---------------|
|  | 53 - 114             | 267                        | I                        | SZKI 209    | 0166154 | 10        | 20        | 30        | 45        | 20        | M6 | 40        | M8     | Steel    | 1.7           |
|                                                                                     | 110 - 184            | 267                        | I                        | SZKI 211    | 0166156 | 10        | 20        | 30        | 45        | 20        | M6 | 40        | M8     | Steel    | 1.4           |

## Claw jaws for O.D. clamping



|                                                                                     | Clamping<br>range ØD | Swing<br>diameter<br>SDmax | Position of<br>base jaws | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|----------------------|----------------------------|--------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|----|-----------|--------|----------|---------------|
|  | 27 - 100             | 268                        | I                        | SZKA 212    | 0139153 | 10        | 20        | 26        | 45        | 25        | M6 | 40        | M8     | Steel    | 1.4           |
|                                                                                     | 136 - 211            | 273                        | I                        | SZKA 216    | 0139159 | 10        | 20        | 30        | 45        | 25        | M6 | 40        | M8     | Steel    | 1.2           |
|                                                                                     | 64 - 138             | 268                        | II                       | SZKA 213    | 0139154 | 10        | 20        | 30        | 45        | 25        | M6 | 40        | M8     | Steel    | 1.3           |




Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for DURO-NCES 200


## Full Grip Jaws

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|------------|-------------|-----------|------------|------------|-----------|------------|-----------|--------|----------|---------------|
|  | SFA-SM 200  | 0173101 | 10        | 20        | 140       | 64         | 200         | 60        | 56         | 50         | 70        | 27         | 40        | M8     | Steel    | 9             |
|                                                                                   | SFA-SM 201  | 0173105 | 10        | 20        | 140       | 64         | 200         | 80        | 76         | 70         | 70        | 27         | 40        | M8     | Steel    | 12.5          |
|  | SFA-SA 200  | 0174101 | 10        | 20        | 140       | 50         | 200         | 58        | 54         | 48         | 72.5      | 32         | 40        | M8     | Aluminum | 3.5           |
|                                                                                   | SFA-SA 201  | 0174105 | 10        | 20        | 140       | 50         | 200         | 80        | 76         | 70         | 72.5      | 32         | 40        | M8     | Aluminum | 4.7           |




## Hard Stepped Block Jaws

|                                                                                   | Description | ID      | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|-----------|----------|---------------|
|  | GST 201     | 0162106 | 22        | 54        | 29         | 84.9      | 8         | Steel    | 1.6           |

## Hard Stepped Top Jaws

|                                                                                     | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHF 200     | 0155101 | 10        | 20        | 22        | 42        | 38         | 71.7      | 10        | 40        | M8     | Steel    | 2.4           |

## Soft Monoblock Jaws



|                                                                                     | Description | ID      | B<br>[mm] | B1<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|------------|-----------|------------|------------|-----------|----------|---------------|
|  | UVB 200     | 0164100 | 22        |            | 65        | 40         |            | 84        | Steel    | 2.7           |
|                                                                                     | UVB-H 200   | 0164116 | 22        |            | 85        | 60         |            | 84        | Steel    | 3.2           |
|  | UVB-B 200   | 0164113 | 22        | 40         | 65        | 38         |            | 84        | Steel    | 3.9           |
|  | UVB-HS 200  | 0164119 | 22        |            | 85        | 60         | 29         | 84        | Steel    | 2.67          |



Technical advice and sales: Tel. +49-7133-103-2750

# SCHUNK chuck jaws for DURO-NCES 200

## Soft Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|------------|-----------|------------|-----------|--------|----------|---------------|
|  | SFA 200     | 0153101 | 10        | 20        | 22        | 47        | 43         |            | 105       | 35         | 40        | M8     | Steel    | 2             |
|                                                                                   | SFA 200-C1  | 0154100 | 10        | 20        | 30        |           | 55.5       | 51.5       | 100       | 23         | 40        | M8     | Steel    | 3.2           |
|                                                                                   | SFA 200-C2  | 0154124 | 10        | 20        | 22        |           | 55.5       | 51.5       | 100       | 23         | 40        | M8     | Steel    | 2.2           |
|                                                                                   | SFA 200-C3  | 0154128 | 10        | 20        | 40        |           | 40         | 36         | 70        | 23         | 40        | M8     | Steel    | 2.1           |
|                                                                                   | SFA 200-C4  | 0154130 | 10        | 20        | 40        |           | 60         | 56         | 85        | 23         | 40        | M8     | Steel    | 4             |
|                                                                                   | SFA 200-C5  | 0154132 | 10        | 20        | 40        |           | 80         | 76         | 95        | 23         | 40        | M8     | Steel    | 6.1           |
|  | SFA-AL 200  | 0172102 | 10        | 20        | 25        | 50        | 46         |            | 105       | 35         | 40        | M8     | Aluminum | 0.9           |



Technical advice and sales: Tel. +49-7133-103-2750